

1

2

3


4

A


B

C

D








Circuit diagram




P.C.B. LAYOUT


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.23	阿树




117




135




150




180




12U




16U




115G



151U



141U



000

DMX-XXXP-X

1:1A以下
3:3A

1:转换型 SPDT	2:常闭型 SPST-NC	3:常开型 SPST-NO
AuGLAR	±5°	
X.	±0.40	
X.x	±0.30	
X.xx	±0.20	
X.xxx	±0.15	
UNSPECIFIED TOLERANCES		



DESIGN	阿树	VIEW:	MODEL TYPE: MICRO SWITCH
CHECKED		UNIT: mm/in	PART NO.: DM3-000P-1
APPROVED		SIZE: A4	DWG NO.: X-DM3-000P-1
			SCALE: N/A
			PAGE: 1/1
			REVISION: A1

1

2

3

4