





| REVISIONS |         |          |                 |            |        |
|-----------|---------|----------|-----------------|------------|--------|
| REV.      | ECN NO. | LOCATION | DESCRIPTION     | DATE       | DESIGN |
| A0        | N/A     |          | INITIAL RELEASE | /          | /      |
| A1        | N/A     |          | 图面升级整理图面        | 2025.12.22 | 阿树     |



- SPECIFICATIONS
- Voltage rating:600V AC/DC
  - Current rating:9A AC/DC
  - Withstanding Voltage:1500V AC/minute
  - Temperature range:-45°C+125°C
  - Insulation resistance:≥1000MΩ
  - Contact resistance:≤10mΩ
  - After environmental testing:≤20mΩ




PART NO.:  
X9357 W V-2x01 FS-N0 SN XX  
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series No  
② Category:W-Wafer  
③ Welding Board Angle:V-Straight 180°  
④ Welding Way:S-SMT  
⑤ Row No-Pin No: 2xXX-2x01P~2x12P  
⑥ Plug the Pin&Specal NO.:FS-The hollow needle with positioning column  
⑦ Material:N0-PA66 94V-0; N2-PA66 94V-2  
⑧ Planting Category:SN-Bright tin plating  
⑨ Color:Blank-natural color

| Poles | Dimensions(mm) |       | Poles | Dimensions(mm) |       |
|-------|----------------|-------|-------|----------------|-------|
|       | A              | B     |       | A              | B     |
| 2x01  | —              | 5.60  | 2x07  | 25.20          | 30.80 |
| 2x02  | 4.20           | 9.80  | 2x08  | 29.40          | 35.00 |
| 2x03  | 8.40           | 14.00 | 2x09  | 33.60          | 39.20 |
| 2x04  | 12.60          | 18.20 | 2x10  | 37.80          | 43.40 |
| 2x05  | 16.80          | 22.40 | 2x11  | 42.00          | 47.60 |
| 2x06  | 21.00          | 26.60 | 2x12  | 46.20          | 51.80 |

Recommended P.C.B Layout  
General Tolerance±0.05



|                     |                   |               |             |                       |
|---------------------|-------------------|---------------|-------------|-----------------------|
| X9357WV-2x01FS-N0SN | Nylon 66 UL 94V-0 | Brass         | Tin-Plated  | X9357H                |
| X9357WV-2xXXFS-N2SN | Nylon 66 UL 94V-2 |               |             |                       |
| PART NO             | Material          | Material(Pin) | Finish(Pin) | Suitable XKB Terminal |

|                        |       |
|------------------------|-------|
| AuGLAR                 | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERANCES |       |



|          |    |             |                                               |
|----------|----|-------------|-----------------------------------------------|
| DESIGN   | 阿树 | VIEW:       | MODEL TYPE:<br>4.20 mm Crimp Style Connectors |
| CHECKED  |    | UNIT: mm/in | PART NO.:<br>X9357WV-2x01FS-N0SN              |
| APPROVED |    | SIZE: A4    | DWG NO.:                                      |