



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.08.04	阿树
/	N/A		/	/	/



PART NO.:

X2009 L-08 B-PT

① ② ③ ④ ⑤

Specification:
Voltage Rating:125V AC/DC
Current Rating :3A AC/DC
Withstaning Voltage:1000V AC/Minute
Temperature Range:-40°~+125°
Insulation Resistance:≥1000MΩ
Contact Resistance:≤24MΩ

①Series Number.
②Special No:L-Lock catch
③Row No.Pin No:XX-02~05Pin
④B:Long style
⑤Material:PT-PBT

Poles	Dimensions(mm)	
	A	B
02	6.30	1.55
03	8.30	
04	10.30	
05	12.30	
06	14.30	1.40
07	16.30	
08	18.30	
09	20.30	
10	22.30	
11	24.30	
12	26.30	
13	28.30	
14	30.30	
15	32.30	

X2009L-08B-PT	PBT	X2000HM-B	X2000W
PART NO	Material	Suitable XKB Housing	Suitable XKB Wafer

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	2.00mm Crimp Style Connectors
CHECKED		UNIT:	mm/in	PART NO.:	X2009L-08B-PT
APPROVED		SIZE:	A4	DWG NO.:	X-X2009L-08B-PT