



REVISION RECORD				
REV	ECN.	DESCRIPTION	DRFT	DATE

UL标准 (UL Standard)

1. 额定电压与电流: 300V/10A
Rated voltage/Rated current: 300V/10A
2. 长期耐压: AC1600V/Min
Withstanding Voltage: AC1600V/Min
3. 线径范围: 28~12AWG
Wire range: 28~12AWG

1. 额定电压与电流

- Rated voltage/Rated current: 320V/20A
2. 線徑範圍: 2.5mm²
Wire range: 2.5mm²

1. 阿婆

2. 使用温度范围: -40℃~+105℃
Operating temperature: -40℃~+105℃
3. 剥线长度: 7~8mm
Stripping length: 7~8mm
4. 符合RoHS环保要求
RoHS Compliance
5. 额定扭矩: 0.4N.m 3.64[Lb. in]
(Rated torque): 0.4N.m 3.64[Lb. in]
6. 未标注公差表
Unimensioned tolerances

刃宽方向公差 (mm)			其他尺寸公差 (mm)					
Pitch range in mm			Nominal dimension range in mm					
≤6	6 ~ 10	10 ~ 24	≤30	30 ~ 60	60 ~ 100	100 ~ 150	≥150	0.1/ ∠
±0.15	±0.20	±0.30	±0.20	±0.30	±0.50	±0.70	±1.00	±1°

MX2EDGKCM -5.08 □ □ P-□ - □ - □ □ □ □

型号 Series NO.	间距 Pitch	极数 Poles	客户型号 Customer Request
------------------	-------------	-------------	--------------------------

1. 单间距
Single Pitch
2. 双间距
Double Pitch
- 颜色(Color)
1. 灰色(Gray) 2. 蓝色(Blue)
3. 黑色(Black) 4. 绿色(Green)
5. 橙色(Orange) 6. 红色(Red)
7. 黄色(Yellow) 8. 白色(White)
9. 透明(Transparent)

4	(Cage)方盒	(Copper alloy) 铜合金	(Ni plated)镀镍	PART NO.: /	 安徽亿思特电子科技有限公司 ANHUI EAST ELECTRONIC TECHNOLOGY CO., LTD.			
3	(Contact)触点	(Copper alloy) 铜合金	(Ni plated)镀镍	APPD: /				
2	(Screw)螺丝 M3	(Steel)钢	(Zn plated)镀锌	CHKD: /	型号	MX2EDGKCM-5.08-XXP-1X-XXAH		
1	(Housing)罩件	PA66	UL94V-0	DRFT: /				
ITEM	NAME OF PART	MATERIAL	NOTES	 THIRD ANGLE PROJECTION	系列	MX2EDGKCM-5.08	页码	1/1
					图号	MX2EDGKCM508001	比例	1:1