

Specifications:


规格:

- 1.Voltage rating:500VAC/DC
额定电压: 500V AC/DC
- 2.Current rating:3A AC/DC
额定电流: 3A AC/DC
- 3.Withstanding voltage:500V AC/minute
耐受电压: $\geq 500V$ AC/分钟
- 4.Temperature range: $-55^{\circ}C$ $-+125^{\circ}C$
温度范围: $-55^{\circ}C$ $-+125^{\circ}C$
- 5.Insulation resistance:1000M Ω MIN
绝缘电阻: $\geq 1000M\Omega$
- 6.Contact resistance:30m Ω Max
接触电阻: $\geq 30m\Omega$

Material:

材料:


- 7.Rubber core:PBT+30%GF UL94V-0
胶芯: PBT + 30%GF UL94V-0
- 8.The iron shell:STEEL Nikvel Plating/
铁壳: STEEL, 镀镍
- 9.Terminal:Brass
端子: 黄铜



PART NO.:

X12 09 W P Z B 1
① ② ③ ④ ⑤ ⑥ ⑦

①Series NO.
②Row No.Pin No.XX-09;15;25;37
③Welding Board Angle :W-Male
④P:Punch-pin
⑤Planting Categoty:7:AuSn
⑥Color:B-BLACK
⑦1:TYPE-1; 2:TYPE-2; 3:TYPE-3;



铆合方式	TYPE-1:铆合	TYPE-2:前铆实心螺母	TYPE-3:后铆空心螺母
图示			

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE: D-SUB
CHECKED		UNIT: mm/in		PART NO.: X1209WP7B1
APPROVED		SIZE: A4		DWG NO.: X-X1209WP7B1
PRECISION CO., LIMITED			SCALE N/A	PAGE 1/1
				REVISION A1