


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.12.1	阿树




Specifications(规格):
1.Voltage rating(额定电压):DC 30V
2.Current rating(额定电流):3A AC/DC
3.Withstanding voltage(耐压值):≥1000V AC/minute
4.Insulation resistance(绝缘电阻):≥1000MΩ Min
5.Contact resistance(接触电阻):≤20mΩ Max
6.Temperature range(使用温度):-40℃~+125℃

PART NO.:

X2514 H I-06 L-0-LD
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No.
- ②Category: H-HSG
- ③Welding Board Angle: I-HSG+hardware
- ④Row No.-Pin No.: XX-Single row
- ⑤L : With Lock
- ⑥0=Tin plated 120~200u" over Ni 30u" overall,for AWG#22~#24
1=Tin plated 120~200u" over Ni 30u" overall,for AWG#26.
G=Gold Flash over Ni 80~150u" overall.
- ⑦See the Table of next page



A=2.5x(No. of circuit-1)
B=A+5.0

X2514HI-06L-0-LD	PA66 94V-0	AWG #22-#24 AWG #26	Phosphor Bronze	X2514W
PART NO	Material	Wire Range	Material (Terminal)	Suitable XKB Terminal
DESIGN	阿树	VIEW:	MODEL TYPE: 4.0mm BTB Connector	
CHECKED		UNIT: mm/in	PART NO.: X2514HI-06L-0-LD	
APPROVED		SIZE: A4	DWG NO.:	
SCALE			PAGE	REVISION
N/A			1/1	A1

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED