





环境试验后: $\leq 20\text{m}\Omega$

X2510WR-04SP-N0SN	Nylon 66 UL 94V-0	Brass	Tin-Plated	X2510H
PART NO	Material	Material(Pin)	Finish(Pin)	Mates With XKB Housing

					ANGLAR	±5°	DWN		DATE		VIEW: 	2.54 mm Crimp Style Connectors
Δx					L ≤ 4	±0.2						PART NO.: X2510WR-04SP-N0SN
Δx					4 < L ≤ 16	±0.3	CHKD		DATE		UNIT: mm/in	
Δx					16 < L ≤ 63	±0.4						DWG NO.: X-X2510WR-04SP-N0SN
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5	APPD		DATE		SIZE: A4	
REVISIONS						UNSPECIFIED TOLERANCES	XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT 1.0g
www.xk-dg.cn www.helloxb.com www.helloxb.cn												SHEET 1/1
												REVISION A0