






	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.03	阿树



SPECIFICATION
 Contact Rating: 50mA, 12V DC
 Contact Resistance: 100m Ω max
 Insulation Resistance: 100M Ω min. 500V DC
 Dielectric Strength: 250V AC/1minute
 Travel: 0.25mm
 Operating Temp: -30 $^{\circ}$ C ~ +85 $^{\circ}$ C
 Storage Temp: -30 $^{\circ}$ C ~ +80 $^{\circ}$ C

PAPT NO	TS-1103ST-B-A
Operating Force	B:160gf C:260gf
Fixed column	A:With B:without
Height	H:7.3



⑤	Terminal	4	Brass (0.30t)	Plating silvering
④	Contact	1	F.ag/SUS	Natural
③	Base	1	Pa46	
②	Cover	1	Spcc	Plating Nickel
①	Keystake	1	Pa46	
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	

XKB 星城
Connection

DESIGN	阿树	VIEW:		MODEL TYPE: TACT SWITCH		
CHECKED		UNIT:	mm/in	PART NO.: TS-1103ST-B-A		
APPROVED		SIZE:	A4	DWG NO.: TS-1103ST-B-A		
PRECISION CO., LIMITED				SCALE N/A	PAGE 1/1	REVISION A1