







|      | REVISIONS |          |                 |            |        |
|------|-----------|----------|-----------------|------------|--------|
| REV. | ECN NO.   | LOCATION | DESCRIPTION     | DATE       | DESIGN |
| A0   | N/A       |          | INITIAL RELEASE | 2024.02.29 | 桑葚     |
| A1   | N/A       |          | 图面升级整理图面        | 2025.12.26 | 阿树     |

Specifications (规格):

1. Voltage rating (额定电压): 250V AC/DC
2. Current rating (额定电流): 3.0A AC/DC
3. Withstanding voltage (耐压值):  $\geq 800V$  AC/minute
4. Insulation resistance (绝缘电阻):  $1000M\Omega$  Min
5. Contact resistance (接触电阻):  $10m\Omega$  Max
6. Temperature range (使用温度):  $-40^{\circ}C \sim +105^{\circ}C$

PART NO.:

X2026   W   V   S-2x02   D1-LP   SW  
 ①   ②   ③   ④   ⑤   ⑥   ⑦   ⑧   ⑨

- ①Series No
- ②Category:W-Wafer
- ③Welding Board Angle:V-Stright 180°
- ④Welding Way: S-SMT
- ⑤Row No.Pin No:2xXX-2x01P~2x22P
- ⑥Plug the Pin&Special NO:  
D1-With Lock in the middle
- ⑦Matiral:LP-LCP;46-PA46
- ⑧Plating Category:SN-Bright Tin Plated  
SW-Fog Tin Plated

| NUMBER OF POSITIONS | DIM.A | DIM.B | DIM.C | NUMBER OF POSITIONS | DIM.A | DIM.B | DIM.C |
|---------------------|-------|-------|-------|---------------------|-------|-------|-------|
| 2X02                | 2.00  | 6.00  | 3.00  | 2X13                | 24.00 | 28.00 | 21.00 |
| 2X03                | 4.00  | 8.00  | 3.00  | 2X14                | 26.00 | 30.00 | 23.00 |
| 2X04                | 6.00  | 10.00 | 3.00  | 2X15                | 28.00 | 32.00 | 25.00 |
| 2X05                | 8.00  | 12.00 | 5.00  | 2X16                | 30.00 | 34.00 | 27.00 |
| 2X06                | 10.00 | 14.00 | 7.00  | 2X17                | 32.00 | 36.00 | 29.00 |
| 2X07                | 12.00 | 16.00 | 9.00  | 2X18                | 34.00 | 38.00 | 31.00 |
| 2X08                | 14.00 | 18.00 | 11.00 | 2X19                | 36.00 | 40.00 | 33.00 |
| 2X09                | 16.00 | 20.00 | 13.00 | 2X20                | 38.00 | 42.00 | 35.00 |
| 2X10                | 18.00 | 22.00 | 15.00 | 2X21                | 40.00 | 44.00 | 37.00 |
| 2X11                | 20.00 | 24.00 | 17.00 | 2X22                | 42.00 | 46.00 | 39.00 |
| 2X12                | 22.00 | 26.00 | 19.00 |                     |       |       |       |

|                      |          |               |             |                       |
|----------------------|----------|---------------|-------------|-----------------------|
| X2026WVS-2x02D1-LPSW | LCP/PA46 | BRASS         | TIN-PLATED  | X2026H-D              |
| PART NO.             | MATERIAL | MATERIAL(PIN) | FINISH(PIN) | Suitable XKB Terminal |

|                        |               |
|------------------------|---------------|
| AuGLAR                 | $\pm 5^\circ$ |
| X.                     | $\pm 0.40$    |
| X.x                    | $\pm 0.30$    |
| X.xx                   | $\pm 0.20$    |
| X.xxx                  | $\pm 0.15$    |
| UNSPECIFIED TOLERAUCES |               |



|          |    |                                                                                             |                                             |
|----------|----|---------------------------------------------------------------------------------------------|---------------------------------------------|
| DESIGN   | 阿树 | VIEW:  | MODEL TYPE:<br>2.00mm Crimp Style Connector |
| CHECKED  |    | UNIT: mm/in                                                                                 | PART NO.:<br>x2026WVS-2x02D1-LPSW           |
| APPROVED |    | SIZE: A4                                                                                    | DWG NO.:                                    |

XKB INDUSTRIAL PRECISION CO.,LIMITED

|       |      |          |
|-------|------|----------|
| SCALE | PAGE | REVISION |
| N/A   | 1/1  | A1       |