



Code-x	H(mm)	H1(mm)	ø(mm)		Code-x	H(mm)	H1(mm)	ø(mm)	
A	4.30	3.15	3.50		O	11.00	9.85	3.00	
B	4.50	3.35				P	11.50		10.35
C	5.00	3.85				Q	12.00		10.85
D	5.50	4.35				R	12.50		11.35
E	6.00	4.85				S	13.00		11.85
F	6.50	5.35	3.40		T	13.50	12.35		
G	7.00	5.85				U	14.00		12.85
H	7.50	6.35				V	15.00		13.35
I	8.00	6.85	3.30		W	15.50	14.35		
J	8.50	7.35				X	16.00		14.85
K	9.00	7.85				Y	17.00		15.85
L	9.50	8.35	3.10		Z	18.00	16.35		
M	10.00	8.85				19	19.00		17.85
N	10.50	9.35			3.00				



PCB.WELDING DRAWING

SPECIFICATION		
Contact Rating:	50mA, 12V DC	
Contact Resistance:	100mΩ max	
Insulation Resistance:	100MΩ min. 500V DC	
Dielectric Strength:	250V AC/1minute	
Travel:	0.25mm	
Operating Temp:	-40℃~+85℃	
Storage Temp:	-40℃~+85℃	

PAPT NO	TC-1102HJ-B-G
Operating Force	A:100gf B:160gf C:260g
Height	Code-X

⑤	Terminal	2	Brass (0.30t)	Plating silvering	
④	Contact	1	F.ag/SUS	Natural	
③	Base	1	PA46		
②	Cover	1	Spcc	Plating Nickel	
①	Keystone	1	PA46		
ITEM	PAPT	NAMF	QTY	MATERIAL	FINISHING

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	

XKIB 星城
Connection

DESIGN	阿树	VIEW:		MODEL TYPE:	TACT SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	TC-1102HJ-B-G
APPROVED		SIZE:	A4	DWG NO.:	TC-1102HJ-B-G
PRECISION CO., LIMITED				SCALE	PAGE
				N/A	1/1
				REVISION	
				A1	