




REVISION RECORD				
REV	ECN.	DESCRIPTION	DRFT	DATE

UL标准 (UL Standard)
1. 额定电压与电流: 300V/15A
Rated voltage/Rated current:300V/15A
2. 功频耐压: AC1600V/Min
Withstanding Voltage:AC1600V/Min
3. 线径范围: 28~12AWG
Wire range:28~12AWG
IEC标准 (IEC Standard)
额定电压与电流: 400V/18A
Rated voltage/Rated current: 400V/18A

NOTE 2:
1. 间距 (Pitch): 7.62mm
2. 使用温度范围: -40℃~+105℃
Operating temperature: -40℃~+105℃
3. 剥线长度: 7~8mm
Stripping length: 7~8mm
4. 符合RoSH环保要求
RoHS Compliance
5. 未标注公差表
Undimensioned tolerances

P距方向公差 (mm)			其他尺寸公差 (mm)							
Pitch range in mm			Nominal dimension range in mm							
≤6	6~10	10~24	≤30	30~60	60~100	100~150	>150		0.1/10	
±0.15	±0.20	±0.30	±0.20	±0.30	±0.50	±0.70	±1.00	±1'		

订购方式 (HOW TO ORDER)
MX2EDGKA-7.62-□□P-□-□-□□□□
型号 间距 极数 客户型号
Series NO. Pitch Poles Customer Request
颜色 (Color)
1. 单间距 Single Pitch
2. 双间距 Double Pitch
1. 灰色 (Gray) 2. 蓝色 (Blue)
3. 黑色 (Black) 4. 绿色 (Green)
5. 橙色 (Orange) 6. 红色 (Red)
7. 黄色 (Yellow) 8. 白色 (White)
9. 透明 (Transparent)

安徽亿思特电子科技有限公司
ANHUI EAST ELECTRONIC TECHNOLOGY CO., LTD.

型号	MX2EDGKA-7.62-XXP-1X-XXAH			
系列	MX2EDGKA-7.62	页码	1/1	
图号	MX2EDGKA762001	比例	1:1	