

1



2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		系列号变更, 图面升级整理图面	2024.11.24	阿树



A




2P
A VIEW

Specification:
Volatage Rating:250V AC/DC
Current Rating :3A AC/DC
Withstaning Voltage:800V AC/Minute
Temperature Range:-40°~+125°
Insulation Resistance:≥1000MΩ
Contact Resistance:≤10MΩ



B



A VIEW



C



PART NO.:

X2000 L-04-PT
① ② ③ ④

- ①Series Number.
②Special No:L-Lock catch
③Row No.Pin No:XX-02~05Pin
④Material:PT-PBT

Poles	Dimensions(mm)	
	A	B
02	2.0	7.3
03	4.0	9.3
04	6.0	11.3
05	8.0	13.3

X2000L-04-PT	PBT	X2000HM	X2000W
PART NO	Material	Suitable XKB Housing	Suitable XKB Wafer

D

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE: 2.0mm Automobile connector
CHECKED		UNIT:	mm/in	PART NO.: X2000L-04-PT
APPROVED		SIZE:	A4	DWG NO.: X2000L-04-PT
		SCALE	PAGE	REVISION
		N/A	1/1	A1

1

2

3

4