


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2026.02.28	
/	N/A		/	/	/



- SPECIFICATIONS
- Voltage rating:50V AC/DC
 - Current rating:1A AC/DC
 - Withstanding Voltage:500V AC/minute
 - Temperature range:-40°C~+125°C
 - Insulation resistance:≥ 100MΩ
 - Contact resistance:≤20mΩ
- Material: Phosphor Bronze
Finish:Plated Tin over all
Applicable wires :AWG#28-#32
Insulation O.D. 0.8mm(Max)

PART NO.:
X1011 I-P SN-A

- 1.Series No
2.Category:T-Terminal
3.Material:P-Phosphor bronze
4.Plating style:SN-Bright tin plating
5.A-Typer A

X1011T-PSN-A	Phosphor bronze	Tin	X1011W	X1011H
PART NO	Material	Plating	Suitable XKB Wafer	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	
CHECKED	
APPROVED	

VIEW: 
UNIT: mm/in
SIZE: A4

MODEL TYPE: 1.0mm Crimp Style Connector
PART NO.: X1011T-PSN-A
DWG NO.: