







SPECIFICATION

1. Rating : DC12V 50mA.
2. Contact resistance: $\leq 100\text{m}\Omega$.
3. Insulation resistance: $\geq 100\text{M}\Omega$ (DC100V).
4. Withstanding voltage: 250VAC .
5. Operating Force: $160 \pm 50\text{gf} / 250 \pm 80\text{gf}$.
6. Travel: $0.25 \pm 0.1\text{mm}$.
7. life test: 100,000 cycles.
8. Operation temperature range: $-25^\circ\text{C} \sim 85^\circ\text{C}$.
9. Sign"* "is importance dimension.


邮箱: hooya89@hooya.hk
电话: 0769-82310511-86



P . C . B L A Y O U T



SCHEMATIC



8					TOLERANCE									
7					UNLESS SPECIFIED									
6					<1.5: $\pm 0.1\text{mm}$	ANGULAR								
5	TERMINAL	BRASS	1	Ag-PLATED	>1.5~5.0: $\pm 0.25\text{mm}$	$\pm 1^\circ$								
4	HOUSING	PPA	1	BLACK	>5.0: $\pm 0.3\text{mm}$		NO	DATE	REVISIONS			BY	APPD	
3	REED	SUS	1	Ag-CLAD	TITLE: TACT SWITCH				UNIT : MM	ROHS	DWN			
2	COVER	BRASS	1	CuSn-PLATED	MODEL: TC-06104H-120E-03				SCALE: 1:1	COMPLIANT	CHK'D			
1	BUTTON	PPA	1		 HOOYAELEC.COM 东莞市弘皓电子有限公司						APPD			
NO.	PART	NAME	MATERIAL	QTY							PRO.AGL:		REV :A0	