






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		pin脚尺寸变更, 图面升级整理图面	2024.11.26	阿树



- SPECIFICATIONS
- Voltage rating:250V AC/DC
 - Current rating:2A AC/DC
 - Withstanding Voltage:1500V AC/minute
 - Temperature range:-40°C~+125°C
 - Insulation resistance:≥1000MΩ
 - Contact resistance:≤20mΩ
- Linetype:AWG#22 AWG#24 AWG#26 AWG#28

Poles	Dimensions(mm)		
	A	B	C
2	2.54	5.08	2.54
3	5.08	7.62	5.08
4	7.62	10.16	7.62
5	10.16	12.70	10.16
6	12.70	15.24	12.70
7	15.24	17.78	15.24
8	17.78	20.32	17.78
9	20.32	22.86	20.32
10	22.86	25.40	22.86
11	25.40	27.94	25.40
12	27.94	30.48	27.94
13	30.48	33.02	30.48
14	33.02	35.56	33.02
15	35.56	38.10	35.56
16	38.10	40.64	38.10
17	40.64	43.18	40.64
18	43.18	45.72	43.18
19	45.72	48.26	45.72
20	48.26	50.80	48.26



PART NO.:

X9254 W R-16-N0 SN XX
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Category:W-Wafer
③Welding Board Angle:R-Stright 90°
④Row No.Pin No:XX-02~30Pin
⑤Material:N0-PA66 UL94V-0
⑥Planting Category:SN-Bright Tin Plated
V01-Gold flash
⑦Color: Blank-Natural Color

X9254WR-XX-NOV01	Nylon 66 UL 94V-0	Brass	Gold flash	X9254H
X9254WR-16-N0SN			Tin-Plated	
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 2.54mm IDC Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X9254WR-16-N0SN
APPROVED		SIZE: A4	DWG NO.: