





| REVISIONS |         |          |                  |            |        |
|-----------|---------|----------|------------------|------------|--------|
| REV.      | ECN NO. | LOCATION | DESCRIPTION      | DATE       | DESIGN |
| A0        | N/A     |          | INITIAL RELEASE  |            |        |
| A1        | N/A     |          | 产品图面修正, 图面升级整理图面 | 2024.08.16 | 阿 树    |



Specifications:  
规格:  
Voltage rating:250V AC/DC  
额定电压: 250V AC/DC  
Current rating:1.5A AC/DC  
额定电流: 1.5A AC/DC  
Withstanding voltage:450V AC/minute  
耐受电压: 500V AC/分钟  
Temperature range:-45℃~+125℃  
温度范围: -45℃~+105℃  
Insulation resistance:1000MΩ min  
绝缘电阻: 1000MΩ Min  
Contact resistance:20mΩ Max  
接触电阻: 20mΩ Max


| Poles | Dimensions |       |
|-------|------------|-------|
|       | A          | B     |
| 06    | 13.34      | 4.00  |
| 08    | 15.34      | 6.00  |
| 10    | 17.34      | 8.00  |
| 12    | 19.34      | 10.00 |
| 14    | 21.34      | 12.00 |
| 16    | 23.34      | 14.00 |
| 18    | 25.34      | 16.00 |
| 20    | 27.34      | 18.00 |
| 22    | 29.34      | 20.00 |
| 24    | 31.34      | 22.00 |
| 26    | 33.34      | 24.00 |
| 28    | 35.34      | 26.00 |
| 30    | 37.34      | 28.00 |
| 32    | 39.34      | 30.00 |
| 34    | 41.34      | 32.00 |
| 36    | 43.34      | 34.00 |
| 40    | 47.34      | 38.00 |
| 42    | 49.34      | 40.00 |
| 44    | 51.34      | 42.00 |
| 50    | 57.34      | 48.00 |
| 60    | 67.34      | 58.00 |
| 64    | 71.34      | 62.00 |
| 68    | 75.34      | 66.00 |



PART NO.:  
X2001 W R-2x13 A-6T V01  
① ② ③ ④ ⑤ ⑥ ⑦  
① Series No  
② Category:W-Wafer  
③ Welding Board Angle:R-Straight 90°  
④ Row No.Pin No:2xXX-2x03-2x32P  
⑤ Category:A-No gap  
⑥ Material:6T-Nylon 6T UL94V-0  
⑦ Plating:V01-Gold Flash

|                     |          |               |                  |
|---------------------|----------|---------------|------------------|
| X2001WR-2x13A-6TV01 | Nylon 6T | Brass         | X2001HA-2xXX     |
|                     |          |               | X2001HA2-2xXX    |
| PART NO             | Material | Material(Pin) | Suitable XKB IDC |

|                        |       |
|------------------------|-------|
| ANGLAR                 | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| *X.xx                  | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERANCES |       |



|                                      |     |       |       |                                     |
|--------------------------------------|-----|-------|-------|-------------------------------------|
| DESIGN                               | 阿 树 | VIEW: |       | MODEL TYPE:<br>2.0mm Jane cattle 筒牛 |
| CHECKED                              |     | UNIT: | mm/in | PART NO.:<br>X2001WR-2x13A-6TV01    |
| APPROVED                             |     | SIZE: | A4    | DWG NO.:<br>X-X2001WR-2x13A-6TV01   |
| XKB INDUSTRIAL PRECISION CO.,LIMITED |     |       |       | SCALE<br>N/A                        |
|                                      |     |       |       | PAGE<br>1/1                         |
|                                      |     |       |       | REVISION<br>A1                      |