




MECHANICAL 机械:


DURABILITY 耐用性: 750 CYCLES MIN.
MATING FORCE 配合力: 23N MAX.
OPERATING TEMPERATURE 工作温度: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
STORAGE TEMPERATURE 储存温度: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
ALL CRITICAL DIMENSIONS WITH “*”

FREE CATALOGUE


TOP VIEW




FRONT VIEW




RIGHT SIDE VIEW




BOTTOM VIEW




RECOMMENDED PCB LAYOUT
VIEWED FROM COMPONENT SIDE



BACK VIEW




LEFT SIDE VIEW



X01AQ106EA2AD5

- 1: Au = 1U"
3: Au = 3U"
4: Au = 6U"
5: Au = 15U"
6: Au = 30U"



LED Specification

Standard LED Color	LED Wavelength	Forward(A)	Forward(V)
Green	568nm	20mA	1.85~2.45V
Yellow	585nm	20mA	1.7~2.2V

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERAuCES	

XTKB 星城 Connection

DESIGN	阿树	VIEW: 	MODEL TYPE: RJ JACK		
CHECKED		UNIT: mm/in	PART NO.: X01AQ106EA2AD5		
APPROVED		SIZE: A4	DWG NO.: X-X01AQ106EA2AD5		
CISION CO., LIMITED			SCALE	PAGE	REVISION
			N/A	1/1	A1