







P.C.B LAYOUT
(TOP VIEW)

Part No.	Dimensions (mm)		
	A	B	C
02P	1.20	4.20	2.65
03P	2.40	5.40	3.85
04P	3.60	6.60	5.05
05P	4.80	7.80	6.25
06P	6.00	9.00	7.45
07P	7.20	10.20	8.65
08P	8.40	11.40	9.85
10P	10.80	13.80	12.25

SPECIFICATIONS

Current Rating: 1.5A AC,DC
Voltage Rating: 50V AC,DC
Temperature Range: -25°C ~ +85°C
Contact Resistance: 20mΩ Max.
Insulation Resistance: 100MΩ Min.
Withstanding Voltage: 500V AC/minute
Pin Material: Phosphor bronze/Gold Flash
Solder Tabs: Phosphor bronze/Tin Plated
Material: Nylon 9T/LCP,UL94V-0
Color: Black



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 1.2压接式针座
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW05-ZHXX-120B
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.
			DRAW NO: HYC-2607291021
			SHEET NO. 1 OF 1