




REVISION RECORD				
REV	ECN.	DESCRIPTION	DRFT	DATE

- NOTE 1:
UL标准 (UL Standard)
1. 额定电压与电流: 300V/2A
Rated voltage/Rated current: 300V/2A
2. 功频耐压: AC1600V/Min
Withstanding Voltage: AC2000V/Min
3. 线径范围: 24~20AWG
Wire range: 24~20AWG
IEC标准 (IEC Standard)
1. 额定电压与电流: 250V/2A
Rated voltage/Rated current: 250V/2A
2. 线径范围: 0.2~0.5mm²
Wire range: 0.2~0.5mm²

- NOTE 2:
1. 间距 (Pitch): 2.50mm
2. 使用温度范围: -40℃~+105℃
Operating temperature: -40℃~+105℃
3. 剥线长度: 8.5~9.5mm
Stripping length: 8.5~9.5mm
4. 符合RoHS环保要求
RoHS Compliance
5. 未标注公差表
Undimensioned tolerances

间距方向公差 (mm) Pitch range in mm		其他尺寸公差 (mm) Nominal dimension range in mm				
≤6	6~10	10~24	≤30	30~60	60~100	100~150
±0.15	±0.20	±0.30	±0.20	±0.30	±0.50	±0.70
±1.00	±1.00	±1.00	±1.00	±1.00	±1.00	±1.00

订购方式 (HOW TO ORDER)

MX250B - 2.50mm - □□P - □ - □ - □□□□

- 型号 Series NO. 间距 Pitch 极数 Poles 客户型号 Customer Request
- 颜色 (Color)
1. 灰色 (Gray) 2. 蓝色 (Blue)
3. 黑色 (Black) 4. 绿色 (Green)
5. 橙色 (Orange) 6. 红色 (Red)
7. 黄色 (Yellow) 8. 白色 (White)
9. 透明 (Transparent)

2	(Pin header) 焊脚	(Copper alloy) 铜合金	(Sn plated) 镀锡
1	(Housing) 壳体	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

PART NO.:	/
APPD:	/
CHKD:	/
DRFT:	/
THIRD ANGLE PROJECTION	



安徽亿思特电子科技有限公司
ANHUI EAST ELECTRONIC TECHNOLOGY CO., LTD.

型号	MX250B-2.50-XXP-1X		
系列	MX250B-2.50	页码	1/1
图号	MX250250001	比例	1:1