






REVISION RECORD				
REV	ECN.	DESCRIPTION	DRFT	DATE



PCB LAYOUT

NOTE 1:

UL标准 (UL Standard)

1. 额定电压与电流: 300V/8A
Rated voltage/Rated current: 300V/8A
2. 功频耐压: AC1600V/Min
Withstanding Voltage: AC1600V/Min

1. 额定电压与电流: 250V/7A
Rated voltage/Rated current: 250V/7A

NOTE 2:

1. 间距(Pitch): 3.81mm
2. 使用温度范围: -40℃~+105℃
Operating temperature: -40℃~+105℃
3. 符合RoSH环保要求
RoHS Compliance
5. 未标注公差表
Undimensioned tolerances

P距方向公差 (mm) Pitch range in mm			其他尺寸公差 (mm) Nominal dimension range in mm						
≤6	6 ~ 10	10 ~ 24	≤30	30 ~ 60	60 ~ 100	100 ~ 150	> 150	0.1/100	
±0.15	±0.20	±0.30	±0.20	±0.30	±0.50	±0.70	±1.00	±1°	

订购方式(HOW TO ORDER)

MX15EDGVM-3.81-□□P-□ - □ - □□□□

型号	间距	极数
Series NO.	Pitch	Poles

客户型号
Customer Request

颜色(Color)

1. 单间距
Single Pitch

2. 双间距
Double Pitch

1. 灰色 (Gray) 2. 蓝色 (Blue)
3. 黑色 (Black) 4. 绿色 (Green)
5. 橙色 (Orange) 6. 红色 (Red)
7. 黄色 (Yellow) 8. 白色 (White)
9. 透明 (Transparent)

N=No.of contacts

2	(Pin header)焊脚	(Copper alloy) 铜合金	(Sn plated)镀锡
1	(Housing)塑件	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

PART NO.:	/	 安徽亿思特电子科技有限公司 ANHUI EAST ELECTRONIC TECHNOLOGY CO., LTD.			
APPD:	/				
CHKD:	/	型号	MX15EDGVM-3.81-XXP-1X		
DRFT:	/				
 THIRD ANGLE PROJECTION		系列	MX15EDGVM-3.81	页码	1/1
		图号	MX15EDGVM381001	比例	1:1

