






MATERIAL:
HOUSING:PA46,PBT,PA66,BLACK.
TERMINAL: PHOSPHOR BRONZE 0.046MM
6/FU*GOLD PLATING


SHIELD:C2680,T=0.20MM, 20 MIN NICKEL 'PLATING
NO ALL AREA

MACHANICAL:
DURABILITY: 750 CYCLES MIN,12.5MM/MINUTE.
INSERTION FORCE: 2.2KG.F MAX.
RETENTION STRENGTH: 7.7KG.F BETWEEN JACK AND PLUG.
OPERATING TEMPERATURE: -40 °C~+85°C.
STORAGE TEMPERATURE: -40°C~+85°C.
ALL CRITICAL DIMENSIONS WITH "±"


VOLTAGE: 125 VOLTS AC.
CURRENT RATING : 1.5AMP.
DIELECTRIC STRENGTH: 1000 VAC RMS 50HZ OR 60HZ,1MIN.
INSULATION RESISTANCE: 500 MEGA OHMS MIN. INITIAL
AFTER 500V DC FOR 1 MINUTE.
CONTACT RESISTANCE: SINGLE TERMINAL 30 MILLIOHMS MAX.
INITIAL 50 MILLIOHMS MAX. AFTER
DURABILITY TEST.

LED Specification

Standard LED Color	LED Wavelength	Foward(A)	Foward(V)
Yellow	568nm	20mA	1.85-2.45V
Green	585nm	20mA	1.7-2.2V



PC Board Layout



			GENERAL TOLERANCE		制图	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL		审核				
			X.X ±0.30		批准	产品名称	网络插座 (带灯无弹)	版本	A
			X.XX ±0.20		CHECK	TITLE		REV.	
1 初版发行			X.XXX ±0.10		APPROVAL	产品料号	HC-RJ45-059C-2x1-2	单位	mm
序号	变更内容	日期	Angle ±3.0°		比例	PART NO.		UNITS	
No.	MODIFY CONTENT	MODIFY DATE	Projection		SCALE	材料		页次	1/1
					投影	MATERIAL		SHEET	