

H
G
F
E
D
C
B
A

REVISION RECORD				
REV	ECN.	DESCRIPTION	DRFT	DATE

- NOTE 1:
UL标准 (UL Standard)
1. 额定电压与电流: 300V/10A
Rated voltage/Rated current: 300V/10A
2. 功频耐压: AC1600V/Min
Withstanding Voltage: AC2000V/Min
3. 线径范围: 30~12AWG
Wire range: 30~12AWG
IEC标准 (IEC Standard)
1. 额定电压与电流: 250V/18A
Rated voltage/Rated current: 250V/18A
2. 线径范围: 2.5mm²
Wire range: 2.5mm²
- NOTE 2:
1. 间距 (Pitch): 5.08mm
2. 使用温度范围: -40℃~+105℃
Operating temperature: -40℃~+105℃
3. 剥线长度: 6~7mm
Stripping length: 6~7mm
4. 符合RoSH环保要求
RoHS Compliance
5. 额定扭矩: 0.4N.m 3.54[Lb. in]
(Rated torque): 0.4N.m 3.54[Lb. in]
6. 未标注公差表
Undimensioned tolerances

Pitch range in mm		Nominal dimension range in mm					
≤6	6~10	10~24	≤30	30~60	60~100	100~150	≥150
±0.15	±0.20	±0.30	±0.20	±0.30	±0.50	±0.70	±1.00

订购方式 (HOW TO ORDER)
MX128DGB- 5.08-□□□□-□-□□□□

型号
Series NO.

间距
Pitch

极数
Poles


客户型号
Customer Request

1. 单间距
Single Pitch

2. 双间距
Double Pitch

颜色 (Color)

1. 灰色 (Gray) 2. 蓝色 (Blue)
3. 黑色 (Black) 4. 绿色 (Green)
5. 橙色 (Orange) 6. 红色 (Red)
7. 黄色 (Yellow) 8. 白色 (White)
9. 透明 (Transparent)



4	(Cage)方盒	(Copper alloy)铜合金	(Ni plated)镀镍	PART NO.: /	安徽亿思特电子科技有限公司 ANHUI EAST ELECTRONIC TECHNOLOGY CO., LTD			
3	(Contact)触点	(Copper alloy)铜合金	(Sn plated)镀锡	APPD: /				
2	(Screw)螺丝 M3	(Steel)钢	(Ni plated)镀镍	CHKD: /	型号	MX128DGB-5.08-XXP-1X-XXAH		
1	(Housing)塑件	PA66	UL94V-0	DRFT: /	系列	MX128DGB-5.08	页码	1/1
ITEM	NAME OF PART	MATERIAL	NOTES	THIED ANGLE PROJECTION	图号	MX128DGB508001	比例	1:1

8 7 6 5 4 3 2 1

8 7 6 5 4 3 2 1