


H
G
F
E
D
C
B
A



PCB LAYOUT

4	(Cage)方盒	(Copper alloy)铜合金	(Ni plated)镀镍
3	(Contact)触点	(Copper alloy)铜合金	(Sn plated)镀锡
2	(Screw)螺丝 M3	(Steel)钢	(Ni plated)镀镍
1	(Housing)塑件	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

PART NO.:	/
APPD:	/
CHKD:	/
DRFT:	/
THIRD ANGLE PROJECTION	

 安徽亿思特电子科技有限公司 ANHUI EAST ELECTRONIC TECHNOLOGY CO., LTD			
型号	MX635-7.62-XXP-1X-XXAH		
系列	MX635-7.62	页码	1/1
图号	MX635762001	比例	1:1

REVISION RECORD				
REV	ECN.	DESCRIPTION	DRFT	DATE

NOTE 1:
UL标准 (UL Standard)
1. 额定电压与电流: 300V/30A
Rated voltage/Rated current: 300V/30A
2. 功频耐压: AC2500V/Min
Withstanding Voltage: AC2000V/Min
3. 线径范围: 26~10AWG
Wire range: 26~10AWG
IEC标准 (IEC Standard)
1. 额定电压与电流: 450V/24A
Rated voltage/Rated current: 450V/24A
2. 线径范围: 1.5~4.0mm²
Wire range: 1.5~4.0mm²
NOTE 2:
1. 间距 (Pitch): 7.62mm
2. 使用温度范围: -40℃~+105℃
Operating temperature: -40℃~+105℃
3. 剥线长度: 8mm
Stripping length: 8mm
4. 符合RoSH环保要求
RoHS Compliance
5. 额定扭矩: 0.5N.m 4.43[Lb. in]
(Rated torque): 0.5N.m 4.43[Lb. in]
6. 未标注公差表
Undimensioned tolerances

P距方向公差 (mm) Pitch range in mm			其他尺寸公差 (mm) Nominal dimension range in mm							
≤6	6 ~ 10	10 ~ 24	≤30	30 ~ 60	60 ~ 100	100 ~ 150	> 150	0.1/10		
±0.15	±0.20	±0.30	±0.20	±0.30	±0.50	±0.70	±1.00	±1'		

订购方式 (HOW TO ORDER)
MX635 - 7.62 - □□P - □ - □□□□
型号 间距 极数 客户型号
Series NO. Pitch Poles Customer Request
颜色 (Color)
1. 单间距 Single Pitch
2. 双间距 Double Pitch
1. 灰色 (Gray) 2. 蓝色 (Blue)
3. 黑色 (Black) 4. 绿色 (Green)
5. 橙色 (Orange) 6. 红色 (Red)
7. 黄色 (Yellow) 8. 白色 (White)
9. 透明 (Transparent)