




REVISION RECORD				
REV	ECN.	DESCRIPTION	DRFT	DATE

NOTE 1:
UL标准 (UL Standard)
1. 额定电压与电流: 300V/8A
Rated voltage/Rated current: 300V/8A
2. 功频耐压: AC1600V/Min
Withstanding Voltage: AC1600V/Min
3. 线径范围: 28~16AWG
Wire range: 28~16AWG
IEC标准 (IEC Standard)
1. 额定电压与电流: 250V/7A
Rated voltage/Rated current: 250V/7A
2. 线径范围: 0.5~1.5 mm²
Wire range: 0.5~1.5 mm²

NOTE 2:
1. 间距 (Pitch): 3.81mm
2. 使用温度范围: -40℃~+105℃
Operating temperature: -40℃~+105℃
3. 剥线长度: 8mm
Stripping length: 8mm
4. 符合RoSE环保要求
RoHS Compliance
5. 未标注公差表
Undimensioned tolerances

间距公差 (mm)		尺寸公差 (mm)				
Pitch range in mm		Nominal dimension range in mm				
≤6	6~10	10~24	≤30	30~60	60~100	100~150
±0.15	±0.20	±0.30	±0.20	±0.30	±0.50	±0.70
±1°	±1°	±1°	±1°	±1°	±1°	±1°

订购方式 (HOW TO ORDER)
MX15EDGKD-3.81-□□P-□-□-□□□□
型号 间距 极数 客户型号
Series NO. Pitch Poles Customer Request
颜色 (Color)
1. 灰色 (Gray) 2. 蓝色 (Blue)
3. 黑色 (Black) 4. 绿色 (Green)
5. 橙色 (Orange) 6. 红色 (Red)
7. 黄色 (Yellow) 8. 白色 (White)
9. 透明 (Transparent)

3	(Spring) 弹片	(Stainless steel) 不锈钢	
2	(Contact) 触点	(Copper alloy) 铜合金	(Ni plated) 镀镍
1	(Housing) 罩件	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

PART NO.: /		 安徽亿思特电子科技有限公司 ANHUI EAST ELECTRONIC TECHNOLOGY CO., LTD.	
APPD: /	CHKD: /		
DRFT: /	THIRD ANGLE PROJECTION	型号	MX15EDGKD-3.81-XXP-1X-XXAH
		系列	MX15EDGKD-3.81
		图号	MX15EDGKD381001
		页码	1/1
		比例	1:1