






PCB LAYOUT

REVISION RECORD				
REV	ECN.	DESCRIPTION	DRFT	DATE

NOTE 1.

UL标准 (UL Standard)

1. 额定电压与电流: 300V/8A
Rated voltage/Rated current: 300V/8A
2. 功频耐压: AC1600V/Min
Withstanding Voltage: AC1600V/Min
3. 线径范围: 22~16AWG
Wire range: 22~16AWG

IEC标准 (IEC Standard)

1. 额定电压与电流: 320V/10A
Rated voltage/Rated current: 320V/10A
2. 线径范围: 0.2~1.5mm²
Wire range: 0.2~1.5mm²

NOTE 2:

- 1. 间距(Pitch): 3.50mm
- 2. 使用温度范围: -40℃~+105℃
Operating temperature: -40℃~+105℃
- 3. 剥线长度: 8.5~9.5mm
Stripping length: 8.5~9.5mm
- 4. 符合RoHS环保要求
RoHS Compliance
- 5. 未标注公差表

Undimensioned tolerances

尺寸方向公差 (mm)				其他尺寸公差 (mm)						
Pitch range in mm				Nominal dimension range in mm						
≤6	6 ~ 10	10 ~ 24		≤30	30 ~ 60	60 ~ 100	100 ~ 150	>150	0.1/1	
									<	
±0.15	±0.20	±0.30		±0.20	±0.30	±0.50	±0.70	±1.00	±1'	

订购方式(HOW TO ORDER)

MX250B- 3.50mm-□□P-□ - □ - □□□□

型号	间距	极数
Series NO.	Pitch	Poles

客户型号
Customer Request

1. 单间距
Single Pitch
2. 双间距
Double Pitch

顏色(Color)

1. 灰色 (Gray) 2. 蓝色 (Blue)
3. 黑色 (Black) 4. 绿色 (Green)
5. 橙色 (Orange) 6. 红色 (Red)
7. 黄色 (Yellow) 8. 白色 (White)
9. 透明 (Transparent)

2	(Pin header)焊脚	(Copper alloy) 铜合金	(Sn plated)镀锡
1	(Housing)塑件	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

PART NO.: /	 安徽亿思特电子科技有限公司 ANHUI EAST ELECTRONIC TECHNOLOGY CO., LTD.															
APPD: /	<table><tr><td>型号</td><td colspan="3">MX250B-3.50-XXP-1X</td></tr><tr><td>系列</td><td>MX250B-3.50</td><td>页码</td><td>1/1</td></tr><tr><td>图号</td><td>MX25035001</td><td>比例</td><td>1:1</td></tr></table>				型号	MX250B-3.50-XXP-1X			系列	MX250B-3.50	页码	1/1	图号	MX25035001	比例	1:1
型号					MX250B-3.50-XXP-1X											
系列					MX250B-3.50	页码	1/1									
图号	MX25035001	比例	1:1													
CHKD: /																
DRFT: /																
 THIRD ANGLE PROJECTION																