





PCB LAYOUT

4	(Cage)方盒	(Copper alloy)铜合金	(Ni plated)镀镍
3	(Contact)触点	(Copper alloy)铜合金	(Sn plated)镀锡
2	(Screw)螺丝 M3	(Steel)钢	(Ni plated)镀镍
1	(Housing)塑件	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES



REVISION RECORD				
REV	ECN.	DESCRIPTION	DRFT	DATE

- NOTE 1:
- UL标准 (UL Standard)
- 额定电压与电流: 300V/30A
Rated voltage/Rated current: 300V/30A
 - 功频耐压: AC2500V/Min
Withstanding Voltage: AC3500V/Min
 - 线径范围: 26~10AWG
Wire range: 26~10AWG
- IEC标准 (IEC Standard)
- 额定电压与电流: 1000V/32A
Rated voltage/Rated current: 1000V/32A
 - 线径范围: 0.2~4.0mm²
Wire range: 0.2~4.0mm²

- NOTE 2:
- 间距 (Pitch): 9.52mm
 - 使用温度范围: -40℃~+105℃
Operating temperature: -40℃~+105℃
 - 剥线长度: 8mm
Stripping length: 8mm
 - 符合RoSH环保要求
RoHS Compliance
 - 额定扭矩: 0.5N.m 4.43[Lb. in]
(Rated torque): 0.5N.m 4.43[Lb. in]
 - 未标注公差表
Undimensioned tolerances

Pitch range in mm		Nominal dimension range in mm					
≤6	6~10	10~24	≤30	30~60	60~100	100~150	>150
±0.15	±0.20	±0.30	±0.20	±0.30	±0.50	±0.70	±1.00

订购方式 (HOW TO ORDER)

MX635- 9.52-□□P-□ - □ - □□□□

- 型号 间距 极数 客户型号
Series NO. Pitch Poles Customer Request
- 颜色 (Color)
- 单间距
Single Pitch
 - 双间距
Double Pitch
 - 灰色 (Gray)
 - 蓝色 (Blue)
 - 黑色 (Black)
 - 绿色 (Green)
 - 橙色 (Orange)
 - 红色 (Red)
 - 黄色 (Yellow)
 - 白色 (White)
 - 透明 (Transparent)



安徽亿思特电子科技有限公司
ANHUI EAST ELECTRONIC TECHNOLOGY CO., LTD

型号	MX635-9.52-XXP-1X-XXAH	页码	1/1
系列	MX635-9.52	比例	1:1
图号	MX635952001		