




UL/CUL 技术 参数 UL/CUL Technical Data				
等 级 Use Group	B	C	D	
额定电压 Rated Voltage [V]	150	-	-	
额定电流 Rated Current [A]	7	-	-	
接线范围 Wire Range 单/多芯线 Solid/Stranded [AWG]	26-18			
耐电压 Withstanding Voltage	1300V/1Min			
IEC 技术参数 IEC Technical Data		IEC60947-7-4		
过电压类别 Overvoltage Category	III	III	II	
污染等级 Contamination Class	3	2	2	
额定电压 Rated Voltage [V]	63	130	320	
额定电流 Rated Current [A]	8	8	8	
额定冲击电压 Impulse withstand voltage [KV]	1.5	1.5	2.5	
导线截面积 Conductor cross section 硬质/柔性导线 Solid/ flexible [mm²]	0.5-1.0			
一般参数 Other Data				
间距 Pitch /极数 Poles [mm] / [P]	2.54/02-24			
剥线长度 Stripping Length [mm]	4-5			
螺丝Screw/扭矩Torque(Max) [N.m]	M1.6/0.1			
工作温度 Operating temperature [°C]	-40~105			
焊锡温度 Soldering temperature	260°C/5S			
符合RoHS环保要求				

Poles	PART NO.	Dimension mm	
		A	B
2	G-DT254S2P-L000	5.54	2.54
3	G-DT254S3P-L000	8.08	5.08
4	G-DT254S4P-L000	10.62	7.62
5	G-DT254S5P-L000	13.16	10.16
6	G-DT254S6P-L000	15.70	12.70
7	G-DT254S7P-L000	18.24	15.24
8	G-DT254S8P-L000	20.78	17.78
...			
24	G-DT254S24-L000	61.42	58.42

4	Screw	Steel	M1.6 Zn/Plated
3	Cage	Copper Alloy	M1.6 Ni/Plated
2	Pin	Copper Alloy	Sn Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:
CHECKED:	DATE:
DRAWN:	DATE:
YKX	2024-5-22

C kmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRY CO., LTD			
TITLE: 绿色端子台 DTEK254-2.54-XP 直针 螺钉式			
PART. NO.		G-DT254SXX-L000	
UNIT	mm	SCALE	free
FILE NO.	Ckmtw-DT254-0008	REV.	A WJ00