


TOLERANCE TABLE	
. 0	± 0.30
. 00	± 0.20
. 000	± 0.05

DATE: _____

DATE: _____

DATE: _____

2026-5-22

UL/CUL 技术 参数 UL/CUL Technical Data																																													
等级 Use Group	B	C	D																																										
额定电压 Rated Voltage [V]	300	-	300																																										
额定电流 Rated Current [A]	16	-	10																																										
接线范围 Wire Range 单/多芯线 Solid/Stranded [AWG]	22-12																																												
耐电压 Withstanding Voltage	1600V/1Min																																												
IEC 技术参数 IEC Technical Data																																													
过电压类别 Overvoltage Category	III	III	II																																										
污染等级 Contamination Class	3	2	2																																										
额定电压 Rated Voltage [V]	450	630	1000																																										
额定电流 Rated Current [A]	20	20	20																																										
额定冲击电压 Impulse withstand voltage [KV]	6.0	6.0	6.0																																										
导线截面积 Conductor cross section 硬质/柔性导线 Solid/ flexible [mm ²]	0.5-2.5																																												
一般参数 Other Data																																													
间距 Pitch /极数 Poles [mm] / [P]	7.62/02-24																																												
剥线长度 Stripping Length [mm]	6-7																																												
螺丝Screw/扭矩Torque(Max) [N.m]	M2.5/0.4																																												
工作温度 Operating temperature [°C]	-40~105																																												
焊锡温度 Soldering temperature	260℃/5S																																												
符合RoHS环保要求																																													
<table border="1"> <tr> <th rowspan="2">Poles</th> <th rowspan="2">PART NO.</th> <th colspan="2">Dimension mm</th> </tr> <tr> <th>A</th> <th>B</th> </tr> <tr> <td>2</td> <td>G-DT12802P-L600</td> <td>15.24</td> <td>7.62</td> </tr> <tr> <td>3</td> <td>G-DT12803P-L600</td> <td>22.86</td> <td>15.24</td> </tr> <tr> <td>4</td> <td>G-DT12804P-L600</td> <td>30.48</td> <td>22.86</td> </tr> <tr> <td>5</td> <td>G-DT12805P-L600</td> <td>38.10</td> <td>30.48</td> </tr> <tr> <td>6</td> <td>G-DT12806P-L600</td> <td>45.72</td> <td>38.10</td> </tr> <tr> <td>7</td> <td>G-DT12807P-L600</td> <td>53.34</td> <td>45.72</td> </tr> <tr> <td>8</td> <td>G-DT12808P-L600</td> <td>60.96</td> <td>53.34</td> </tr> <tr> <td>...</td> <td></td> <td></td> <td></td> </tr> <tr> <td>24</td> <td>G-DT12824P-L600</td> <td>182.88</td> <td>175.26</td> </tr> </table>				Poles	PART NO.	Dimension mm		A	B	2	G-DT12802P-L600	15.24	7.62	3	G-DT12803P-L600	22.86	15.24	4	G-DT12804P-L600	30.48	22.86	5	G-DT12805P-L600	38.10	30.48	6	G-DT12806P-L600	45.72	38.10	7	G-DT12807P-L600	53.34	45.72	8	G-DT12808P-L600	60.96	53.34	...				24	G-DT12824P-L600	182.88	175.26
Poles	PART NO.	Dimension mm																																											
		A	B																																										
2	G-DT12802P-L600	15.24	7.62																																										
3	G-DT12803P-L600	22.86	15.24																																										
4	G-DT12804P-L600	30.48	22.86																																										
5	G-DT12805P-L600	38.10	30.48																																										
6	G-DT12806P-L600	45.72	38.10																																										
7	G-DT12807P-L600	53.34	45.72																																										
8	G-DT12808P-L600	60.96	53.34																																										
...																																													
24	G-DT12824P-L600	182.88	175.26																																										
 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRY CO., LTD																																													
TITLE:																																													
绿色端子台 DT128-7.62-XP 直插 螺钉式																																													
PART.NO.		G-DT128XXP-L600																																											
UNIT	mm	SCALE	free																																										
FILE NO.	Ckmtw-DT762-0010	REV.	A WJ00																																										