







5	Button	Pom	UL94-HB
4	Clamp	Copper Alloy	Sn Plated
3	Spring	Stainless Steel	/
2	Cover	PA66	UL94V-0
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:
CHECKED:	DATE:
DRAWN:	DATE:
YKX	2024-5-21

UL/CUL 技术 参数 UL/CUL Technical Data					
等 级 Use Group		B	C	D	
额定电压 Rated Voltage [V]		300	-	300	
额定电流 Rated Current [A]		8	-	8	
接线范围 Wire Range 单/多芯线 Solid/Stranded [AWG]		28-16			
耐电压 Withstanding Voltage		1600V/1Min			
IEC 技术参数 IEC Technical Data					
过电压类别 Overvoltage Category		III	III	II	
污染等级 Contamination Class		3	2	2	
额定电压 Rated Voltage [V]		160	160	320	
额定电流 Rated Current [A]		8	8	8	
额定冲击电压 Impulse withstand voltage [KV]		2.5	2.5	2.5	
导线截面积 Conductor cross section 硬质/柔性导线 Solid/ flexible [mm²]		0.2-1.5			
一般参数 Other Data					
间距 Pitch /极数 Poles [mm] / [P]		3.81 / 02-24			
剥线长度 Stripping Length [mm]		7-8			
工作温度 Operating temperature [°C]		-40~105			
符合RoHS环保要求					

Poles	PART NO.	Dimension mm	
		A	B
2	G-DT38K02P-CD00	8.41	3.81
3	G-DT38K03P-CD00	12.22	7.62
4	G-DT38K04P-CD00	16.03	11.43
5	G-DT38K05P-CD00	19.84	15.24
6	G-DT38K06P-CD00	23.65	19.05
...			
24	G-DT38K24P-CD00	92.23	87.63

Ckmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRY CO., LTD			
TITLE: 绿色端子台 DT15EDGKD-3.81-XP 直母头 按压式			
PART. NO.		G-DT38KXXP-CD00	
UNIT	mm	SCALE	free
FILE NO.	Ckmtw-DT381-0013	REV.	A WJ00