





2P视图

5	Button	Pom	UL94-HB
4	Clamp	Copper Alloy	Sn Plated
3	Spring	Stainless Steel	/
2	Cover	PA66	UL94V-0
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: 绿色端子台 DT250KD-2.5-XP 直母座 按压式			
DRAWN: YKX	DATE: 2024-5-22	PART. NO.		G-DT25KXXP-D000	
		UNIT	mm	SCALE	free
		FILE NO.		Ckmtw-DT250-0001	REV. A WJ00

UL/CUL 技术 参数 UL/CUL Technical Data					
等 级 Use Group	B	C	D		
额定电压 Rated Voltage [V]	150	-	-		
额定电流 Rated Current [A]	5	-	-		
接线范围 Wire Range 单/多芯线 Solid/Stranded [AWG]	26-20				
耐电压 Withstanding Voltage	1300V/1Min				
IEC 技术参数 IEC Technical Data			IEC61984		
过电压类别 Overvoltage Category	III	III	II		
污染等级 Contamination Class	3	2	2		
额定电压 Rated Voltage [V]	100	160	320		
额定电流 Rated Current [A]	5	5	5		
额定冲击电压 Impulse withstand voltage [KV]	1.5	2.5	2.5		
导线截面积 Conductor cross section 硬质/柔性导线 Solid/ flexible [mm²]	0.2-0.5				
一般参数 Other Data					
间距 Pitch /极数 Poles [mm] / [P]	2.5/02-24				
剥线长度 Stripping Length [mm]	7-8				
工作温度 Operating temperature [°C]	-40~105				
符合RoHS环保要求					

Poles	PART NO.	Dimension mm		
		A	B	C
2	G-DT25K02P-D000	5.00	2.50	5.60
3	G-DT25K03P-D000	7.50	5.00	8.10
4	G-DT25K04P-D000	10.00	7.50	10.60
5	G-DT25K05P-D000	12.50	10.00	13.10
6	G-DT25K06P-D000	15.00	12.50	15.60
7	G-DT25K07P-D000	17.50	15.00	18.10
8	G-DT25K08P-D000	20.00	17.50	20.60
...	...	...	...	...
24	G-DT25K24P-D000	60.00	57.50	60.60