








技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
3. 额定电压: 50V, AC.
4. 接触电阻: $\leq 0.02\Omega$.
5. 绝缘电阻: $\geq 100M\Omega$



序号	品名	材质
①	0.5 Pitch双槽立式BTB母座胶芯	PA10T UL94 V-0 颜色:黑色
②	0.5 Pitch双槽立式BTB母座端子	铜合金/表面点镀金
③	0.5 Pitch双槽立式BTB母座吸盖	LCP UL94 V-0 颜色:黑色

High photosynthesis 合高 (H)	The female seat neight 母座单高 (H1)	The male seat neight 公座单高 (H2)	Insertion height (H3)
3.00	2.20	0.80	1.60
3.50	2.20	1.30	1.60
4.00	3.00	1.00	1.90
4.50	3.50	1.00	1.90
5.00	4.00	1.00	1.90
5.50	4.50	1.00	1.90
6.00	4.00	2.00	1.90
6.50	4.50	2.00	1.90
7.00	3.00	4.00	1.90
7.50	3.50	4.00	1.90
8.00	4.00	4.00	1.90
8.50	4.50	4.00	1.90

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENE RL TOL E RANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-BTB0.5-30HMA1-XPLT		版本 REV.	A	
			X.	±0.50	X.°	±1°	LEO			品名 TITLE	0.5 Pitch双槽立式BTB母(单高3.0)		页次 SHEET	1/2
			X.X	±0.20			JOHN			客户料号 CUTM.NO.				
			X.XX	±0.10						 兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.				
							单位 UNITS	MM	比例 SCALE	1:1				
