






UL/CUL 技术 参数 UL/CUL Technical Data					
等 级 Use Group	B	C	D		
额定电压 Rated Voltage [V]	300	—	300		
额定电流 Rated Current [A]	8	—	8		
接线范围 Wire Range 单/多芯线 Solid/Stranded [AWG]	28-16				
耐电压 Withstanding Voltage	1600V/1Min				
IEC 技术参数 IEC Technical Data					
过电压类别 Overvoltage Category	III	III	II		
污染等级 Contamination Class	3	2	2		
额定电压 Rated Voltage [V]	160	160	320		
额定电流 Rated Current [A]	8	8	8		
额定冲击电压 Impulse withstand voltage [KV]	2.5	2.5	2.5		
导线截面积 Conductor cross section 硬质/柔性导线 Solid/ flexible [mm ²]	0.2-1.5				
一般参数 Other Data					
间距 Pitch /极数 Poles [mm] / [P]	3.81/02-24				
剥线长度 Stripping Length [mm]	6-7				
螺丝 Screw/扭矩 Torque (Max) [N.m]	M2/0.2				
工作温度 Operating temperature [°C]	-40~105				
符合RoHS环保要求					

Poles	PART NO.	Dimension mm	
		A	B
2	G-DT38K02P-CB00	8.41	3.81
3	G-DT38K03P-CB00	12.22	7.62
4	G-DT38K04P-CB00	16.03	11.43
5	G-DT38K05P-CB00	19.84	15.24
6	G-DT38K06P-CB00	23.65	19.05
...			
24	G-DT38K24P-CB00	92.23	87.63

5	Clamp	Copper Alloy	Sn Plated
4	Screw	Steel	M2/Zn Plated
3	Cage	Copper Alloy	M2/Ni Plated
2	Cover	PA66	UL94V-0
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

TOLERANCE TABLE			
.0	±0.30		
.00	±0.20		
.000	±0.05		

APPROVED:	DATE:	深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: 绿色端子台 DT15EDGKB-3.81-XP 直母头			
DRAWN: YKX	DATE: 2024-5-22	PART. NO.		G-DT38KXXP-CB00	
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-DT381-0012	REV.	A WJ00