




5	Screw	Steel	M1.6/Zn Plaed
4	Cage	Copper Alloy	M1.6/Ni Plaed
3	Clamp	Copper Alloy	Sn Plated
2	Cover	PA66	UL94V-0
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:
CHECKED:	DATE:
DRAWN:	DATE:
YKX	2024-5-22

UL/CUL 技术 参数 UL/CUL Technical Data					
等 级 Use Group	B	C	D		
额定电压 Rated Voltage [V]	150	-	-		
额定电流 Rated Current [A]	5	-	-		
接线范围 Wire Range 单/多芯线 Solid/Stranded [AWG]	26-20				
耐电压 Withstanding Voltage	1300V/1min				
IEC 技术参数 IEC Technical Data				IEC61984	
过电压类别 Overvoltage Category	III	III	II		
污染等级 Contamination Class	3	2	2		
额定电压 Rated Voltage [V]	100	160	320		
额定电流 Rated Current [A]	5	5	5		
额定冲击电压 Impulse withstand voltage [KV]	1.5	2.5	2.5		
导线截面积 Conductor cross section 硬质/柔性导线 Solid/ flexible [mm ²]	0.2-0.5				
一般参数 Other Data					
间距 Pitch /极数 Poles [mm] / [P]	2.54 / 02-24				
剥线长度 Stripping Length [mm]	5-6				
螺丝 Screw	M1.6				
扭矩 Torque(Max) [N.m]	0.1				
工作温度 Operating temperature [°C]	-40~105				
符合RoHS环保要求					

Poles	PART NO.	Dimension mm	
		A	B
2	G-DT254K2P-C000	5.68	2.54
3	G-DT254K3P-C000	8.22	5.08
4	G-DT254K4P-C000	10.76	7.62
5	G-DT254K5P-C000	13.30	10.16
6	G-DT254K6P-C000	15.84	12.70
7	G-DT254K7P-C000	18.38	15.24
8	G-DT254K8P-C000	20.92	17.78
...	...	...	...
24	G-DT254K24-C000	61.56	58.42

C kmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRY CO.,LTD					
TITLE: 绿色端子台 DT15EDGK-2.54-XP 弯母头					
PART. NO.		G-DT254KXX-C000			
UNIT	mm	SCALE	free		
FILE NO.	Ckmtw-DT254-0006	REV.	A	WJ00	