







P.C.B. LAYOUT



UL/CUL 技术 参数 UL/CUL Technical Data			
等 级 Use Group	B	C	D
额定电压 Rated Voltage [V]	300	-	300
额定电流 Rated Current [A]	10	-	10
接线范围 Wire Range单/多芯线 Solid/Stranded [AWG]	28-16		
耐电压 Withstanding Voltage	1600V/1Min		
IEC 技术参数 IEC Technical Data			
过电压类别 Overvoltage Category	III	III	II
污染等级 Contamination Class	3	2	2
额定电压 Rated Voltage [V]	160	200	400
额定电流 Rated Current [A]	13.5	13.5	13.5
额定冲击电压 Impulse withstand voltage [KV]	2.5	2.5	2.5
导线截面积 Conductor cross section 硬质/柔性导线 Solid/ flexible [mm²]	0.5-1.0		
一般参数 Other Data			
间距 Pitch /极数 Poles [mm] / [P]	3.5/02-24		
剥线长度 Stripping Length [mm]	4-5		
螺丝Screw/扭矩Torque(Max) [N.m]	M2/0.2		
工作温度 Operating temperature [°C]	-40~105		
焊锡温度 Soldering temperature	260°C/5S		
符合RoHS环保要求			

Poles	PART NO.	Dimension mm	
		A	B
2	G-DT35S02P-L000	7.00	3.50
3	G-DT35S03P-L000	10.50	7.00
4	G-DT35S04P-L000	14.00	10.50
5	G-DT35S05P-L000	17.50	14.00
6	G-DT35S06P-L000	21.00	17.50
...			
24	G-DT35S24P-L000	84.00	80.50

4	Header Pin	Copper Alloy	Sn Plated
3	Screw	Steel	M2/Zn Plated
2	Cage	Copper Alloy	M2/Ni Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRYCO., LTD						
CHECKED:	DATE:	TITLE: 绿色端子台 DTEK350-3.5-xP 直针 螺钉式						
DRAWN: YKX	DATE: 2026-5-22	PART. NO.		G-DT35SXXP-L000				
		UNIT	mm	SCALE	free			
		FILE NO.		Ckmtw-DT350-0016		REV.	A	WJ00