





PCB LAYOUT

2	Pin	Copper Alloy	Sn Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:
CHECKED:	DATE:
DRAWN:	DATE:
YKX	2024-5-22

UL/CUL 技术 参数 UL/CUL Technical Data					
等 级 Use Group	B	C	D		
额定电压 Rated Voltage [V]	300	—	300		
额定电流 Rated Current [A]	8	—	8		
接线范围 Wire Range 单/多芯线 Solid/Stranded [AWG]	—				
耐电压 Withstanding Voltage	1600V/1Min				
IEC 技术参数 IEC Technical Data					
过电压类别 Overvoltage Category	III	III	II		
污染等级 Contamination Class	3	2	2		
额定电压 Rated Voltage [V]	160	160	250		
额定电流 Rated Current [A]	7	7	7		
额定冲击电压 Impulse withstand voltage [KV]	2.5	2.5	2.5		
导线截面积 Conductor cross section 硬质/柔性导线 Solid/ flexible [mm ²]	—				
一般参数 Other Data					
间距 Pitch /极数 Poles [mm] / [P]	3.5/02-24				
工作温度 Operating temperature [°C]	-40~105				
焊锡温度 Soldering temperature	260°C/5S				
引针尺寸 Pin Dimensions [mm]	0.8*0.8				
PCB板孔径 PCB Hole Diameter [mm]	φ 1.4				
符合RoHS环保要求					

Poles	PART NO.	Dimension mm	
		A	B
2	G-DT35S02P-C000	7.80	3.50
3	G-DT35S03P-C000	11.30	7.00
4	G-DT35S04P-C000	14.80	10.50
5	G-DT35S05P-C000	18.30	14.00
6	G-DT35S06P-C000	21.80	17.50
...			
24	G-DT35S24P-C000	84.80	80.50

Ckmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRYCO., LTD						
TITLE: 绿色端子台 DT15EDGVC-3.5-XP 直针座 封口						
PART. NO.		G-DT35SXXP-C000				
UNIT	mm	SCALE	free			
FILE NO.	Ckmtw-DT350-0015	REV.	A	WJ00		