






5	Button	Pom	UL94-HB
4	Clamp	Copper Alloy	Sn Plated
3	Spring	Stainless Steel	/
2	Cover	PA66	UL94V-0
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:
CHECKED:	DATE:
DRAWN:	DATE:
YKX	2024-5-22

UL/CUL 技术 参数 UL/CUL Technical Data					
等 级 Use Group	B	C	D		
额定电压 Rated Voltage [V]	300	—	300		
额定电流 Rated Current [A]	5	—	8		
接线范围 Wire Range 单/多芯线 Solid/Stranded [AWG]	28-16				
耐电压 Withstanding Voltage	1600V/1Min				
IEC 技术参数 IEC Technical Data					
过电压类别 Overvoltage Category	III	III	II		
污染等级 Contamination Class	3	2	2		
额定电压 Rated Voltage [V]	160	160	320		
额定电流 Rated Current [A]	8	8	8		
额定冲击电压 Impulse withstand voltage [KV]	2.5	2.5	2.5		
导线截面积 Conductor cross section 硬质/柔性导线 Solid/ flexible [mm ²]	0.2-1.5				
一般参数 Other Data					
间距 Pitch /极数 Poles [mm] / [P]	3.5/02-24				
剥线长度 Stripping Length [mm]	7-8				
工作温度 Operating temperature [°C]	-40~105				
符合RoHS环保要求					

Poles	PART NO.	Dimension mm	
		A	B
2	G-DT35K02P-CD00	7.90	3.50
3	G-DT35K03P-CD00	11.40	7.00
4	G-DT35K04P-CD00	14.90	10.50
5	G-DT35K05P-CD00	18.40	14.00
6	G-DT35K06P-CD00	21.90	17.50
...			
24	G-DT35K24P-CD00	84.90	80.50

Ckmtw		深圳市灿科盟实业有限公司 CANKEMENG INDUSTRY CO., LTD			
TITLE:		绿色端子台 DT15EDGKD-3.5-XP 直母头 按压式			
PART. NO.		G-DT35KXXP-CD00			
UNIT	mm	SCALE	free		
FILE NO.	Ckmtw-DT350-0013	REV.	A	WJ00	