






Poles	PART NO.	Dimension mm	
		A	B
2	G-DT508K2P-C000	10.16	5.08
3	G-DT508K3P-C000	15.24	10.16
4	G-DT508K4P-C000	20.32	15.24
5	G-DT508K5P-C000	25.40	20.32
6	G-DT508K6P-C000	30.48	25.40
7	G-DT508K7P-C000	35.56	30.48
8	G-DT508K8P-C000	40.64	35.56
...			
24	G-DT508K24-C000	121.92	116.84

UL/CUL 技术 参数

UL/CUL Technical Data



等 级 Use Group	B	C	D
额定电压 Rated Voltage [V]	300	-	300
额定电流 Rated Current [A]	15	-	10
接线范围 Wire Range 单/多芯线 Solid/Stranded [AWG]	28-12		
耐电压 Withstanding Voltage	1600V/1Min		

IEC 技术参数

IEC Technical Data



过电压类别 Overvoltage Category	III	III	II
污染等级 Contamination Class	3	2	2
额定电压 Rated Voltage [V]	250	320	630
额定电流 Rated Current [A]	15	15	15
额定冲击电压 Impulse withstand voltage [KV]	4.0	4.0	4.0
导线截面积 Conductor cross section 硬质/柔性导线 Solid/ flexible [mm ²]	0.2-2.5		

一般参数 Other Data

间距 Pitch /极数 Poles [mm] / [P]	5.08/02-24
剥线长度 Stripping Length [mm]	7-8
螺丝 Screw	M3
扭矩 Torque (Max) [N.m]	0.5
工作温度 Operating temperature [°C]	-40~105
符合RoHS环保要求	

5	Clamp	Copper Alloy	Sn Plated
4	Screw	Steel	M3/Zn Plaed
3	Cage	Copper Alloy	Ni Plaed
2	Cover	PA66	UL94V-0
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRY CO., LTD						
CHECKED:	DATE:	TITLE: 绿色端子台 DT2EDGK-5.08-XP 弯母头						
DRAWN: YKX	DATE: 2026-5-22	PART. NO.		G-DT508KXP-C000				
		UNIT	mm	SCALE	free			
		FILE NO.		Ckmtw-DT508-0020		REV.	A	WJ00