






5	Button	Pom	UL94-HB
4	Clamp	Copper Alloy	Sn Plated
3	Spring	Stainless Steel	/
2	Cover	PA66	UL94V-0
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: 绿色端子台 DT2EDGKD-5.08-XP 弯母头 接压式			
DRAWN: YKX	DATE: 2026-5-22	PART. NO.		G-DT508KXP-CD00	
		UNIT	mm	SCALE	free
		FILE NO.		Ckmtw-DT508-0021	REV. A WJ00

UL/CUL 技术 参数
UL/CUL Technical Data

等 级 Use Group	B	C	D
额定电压 Rated Voltage [V]	300	-	300
额定电流 Rated Current [A]	10	-	10
接线范围 Wire Range 单/多芯线 Solid/Stranded [AWG]	28-12		
耐电压 Withstanding Voltage	1600V/1Min		
IEC 技术参数 IEC Technical Data			
过电压类别 Overvoltage Category	III	III	II
污染等级 Contamination Class	3	2	2
额定电压 Rated Voltage [V]	250	320	630
额定电流 Rated Current [A]	12	12	12
额定冲击电压 Impulse withstand voltage [KV]	4.0	4.0	4.0
导线截面积 Conductor cross section 硬质/柔性导线 Solid/ flexible [mm ²]	0.2-2.5		
一般参数 Other Data			
间距 Pitch /极数 Poles [mm] / [P]	5.08/02-24		
剥线长度 Stripping Length [mm]	7-8		
工作温度 Operating temperature [°C]	-40~105		
符合RoHS环保要求			

Poles	PART NO.	Dimension mm		
		A	B	C
2	G-DT508K2P-CD00	10.76	5.08	10.16
3	G-DT508K3P-CD00	15.84	10.16	15.24
4	G-DT508K4P-CD00	20.92	15.24	20.32
5	G-DT508K5P-CD00	26.00	20.32	25.40
6	G-DT508K6P-CD00	31.08	25.40	30.48
7	G-DT508K7P-CD00	36.16	30.48	35.56
8	G-DT508K8P-CD00	41.24	35.56	40.64
...				
24	G-DT508K24-CD00	122.52	116.84	121.92