






UL/CUL 技术 参数
UL/CUL Technical Data



等 级 Use Group	B	C	D
额定电压 Rated Voltage [V]	300	-	300
额定电流 Rated Current [A]	8	-	8
接线范围 Wire Range 单/多芯线 Solid/Stranded [AWG]	28-16		
耐电压 Withstanding Voltage	1600V/1Min		

IEC 技术参数
IEC Technical Data



过电压类别 Overvoltage Category	III	III	II
污染等级 Contamination Class	3	2	2
额定电压 Rated Voltage [V]	160	160	320
额定电流 Rated Current [A]	8	8	8
额定冲击电压 Impulse withstand voltage [kV]	2.5	2.5	2.5
导线截面积 Conductor cross section 硬质/柔性导线 Solid/ flexible [mm ²]	0.2-1.5		

一般参数 Other Data

间距 Pitch /极数 Poles [mm] / [P]	3.5/02-24
剥线长度 Stripping Length [mm]	6-7
螺丝 Screw/扭矩 Torque(Max) [N.m]	M2/0.2
工作温度 Operating temperature [°C]	-40~105

符合RoHS环保要求

Poles	PART NO.	Dimension mm	
		A	B
2	G-DT35K02P-CB00	7.80	3.50
3	G-DT35K03P-CB00	11.30	7.00
4	G-DT35K04P-CB00	14.80	10.50
5	G-DT35K05P-CB00	18.30	14.00
6	G-DT35K06P-CB00	21.80	17.50
...			
24	G-DT35K24P-CB00	84.80	80.50

5	Clamp	Copper Alloy	Sn Plated
4	Screw	Steel	M2/Zn Plated
3	Cage	Copper Alloy	M2/Ni Plated
2	Cover	PA66	UL94V-0
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:

DATE:

CHECKED:

DATE:

DRAWN:

DATE:

YKX

2024-5-22

Ckmtw 深圳市灿科盟实业有限公司
CHANKEMENG INDUSTRY CO., LTD

TITLE:
绿色端子台 DT15EDGKB-3.5-XP 直母头

PART. NO. G-DT35KXXP-CB00

UNIT mm SCALE free

FILE NO. Ckmtw-DT350-0012 REV. A WJ00