





UL/CUL 技术 参数 UL/CUL Technical Data					
等 级 Use Group	B		C	D	
额定电压 Rated Voltage [V]	300		150	300	
额定电流 Rated Current [A]	20		20	10	
接线范围 Wire Range 单/多芯线 Solid/Stranded [AWG]	26-12				
耐电压 Withstanding Voltage	1600V/1Min				
IEC 技术参数 IEC Technical Data					
过电压类别 Overvoltage Category	III		III	II	
污染等级 Contamination Class	3		2	2	
额定电压 Rated Voltage [V]	450		630	100	
额定电流 Rated Current [A]	24		24	24	
额定冲击电压 Impulse withstand voltage [KV]	6.0		6.0	6.0	
导线截面积 Conductor cross section 硬质/柔性导线 Solid/ flexible [mm²]	0.5-2.5				
一般参数 Other Data					
间距 Pitch /极数 Poles [mm] / [P]			7.62/02-24		
剥线长度 Stripping Length [mm]			6-7		
螺丝Screw/扭矩Torque(Max) [N.m]			M3/0.5		
工作温度 Operating temperature [°C]			-40~105		
焊锡温度 Soldering temperature			260℃/5S		
符合RoHS环保要求					
Poles	PART NO.	Dimension mm			
		A	B		
2	G-DT12902P-L600	15.24	7.62		
3	G-DT12903P-L600	22.86	15.24		
4	G-DT12904P-L600	30.48	22.86		
5	G-DT12905P-L600	38.10	30.48		
6	G-DT12906P-L600	45.72	38.10		
7	G-DT12907P-L600	53.34	45.72		
8	G-DT12908P-L600	60.96	53.34		
...					
24	G-DT12924P-L600	182.88	175.26		

 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRY CO., LTD			
TITLE: 绿色端子台 DT129-7.62-XP 直插 螺钉式			
PART. NO.		G-DT129XXP-L600	
UNIT	mm	SCALE	free
FILE NO.	Ckmtw-DT762-0011	REV.	A WJ00



P.C.B. LAYOUT



4	Header Pin	Copper Alloy	Sn Plated
3	Screw	Steel	M3/Zn Plated
2	Cage	Copper Alloy	M3/Ni Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:
CHECKED:	DATE:
DRAWN:	DATE:
YKX	2026-5-22