







P.C.B. LAYOUT



UL/CUL 技术 参数
UL/CUL Technical Data



等 级 Use Group	B	C	D
额定电压 Rated Voltage [V]	300	-	300
额定电流 Rated Current [A]	15	-	10
接线范围 Wire Range 单/多芯线 Solid/Stranded [AWG]	-		
耐电压 Withstanding Voltage	1600V/1Min		

IEC 技术参数
IEC Technical Data



过电压类别 Overvoltage Category	III	III	II
污染等级 Contamination Class	3	2	2
额定电压 Rated Voltage [V]	250	320	630
额定电流 Rated Current [A]	15	15	15
额定冲击电压 Impulse withstand voltage [KV]	4.0	4.0	4.0
导线截面积 Conductor cross section 硬质/柔性导线 Solid/ flexible [mm ²]	-		

一般参数 Other Data

间距 Pitch /极数 Poles [mm] / [P]	5.08/02-24
工作温度 Operating temperature [°C]	-40~105
焊锡温度 Soldering temperature	260°C/5S
引针尺寸 Pin Dimensions [mm]	1.0*1.0
PCB板孔径 PCB Hole Diameter [mm]	φ 1.7

符合RoHS环保要求

Poles	PART NO.	Dimension mm	
		A	B
2	G-DT508R2P-C000	11.56	5.08
3	G-DT508R3P-C000	16.64	10.16
4	G-DT508R4P-C000	21.72	15.24
5	G-DT508R5P-C000	26.80	20.32
6	G-DT508R6P-C000	31.88	25.40
7	G-DT508R7P-C000	36.96	30.48
8	G-DT508R8P-C000	42.04	35.56
...			
24	G-DT508R24-C000	123.32	116.84

APPROVED:

DATE:

CHECKED:

DATE:

DRAWN:

YKX

DATE:

2026-5-22

Ckmtw 深圳市灿科盟实业有限公司
CANKEMENG INDUSTRY CO., LTD

TITLE:
绿色端子台 DT2EDGRC-5.08-XP 弯针 封口

PART. NO. G-DT508RXP-C000

UNIT mm SCALE free

FILE NO. Ckmtw-DT508-0023 REV. A WJ00

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

2	Pin	Copper Alloy	Sn Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES