

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA9T+30%G.F UL94V-0, Color: Black

四方针: 黄铜, 镍底30u"MIN, 表面镀普金

Contact: Brass, GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Rated Current: 3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.





Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C



Ordering Information

P125-12 03 A0 C S 155 B 1

HEIGHT OF HOUSING	NO. OF PINS PER ROW	Contact Full of Gold	Plating Serial-gold	INSULATOR MATERIAL	LENGTH OF TERMINAL	PACKING
15: 1.5mm	2~40P	A0=0.8u"	B0=0.8u"	A: PBT		A: PE Bag
17: 1.7mm		A1=1u"	B1=1u"	B: PA6T		B: Tape & Reel
20: 2.0mm		A2=1.5u"	B2=1.5u"	C: PA9T		C: Tube
25: 2.54mm		A3=2u"	B3=2u"	D: LCP		D: Tube+CAP
30: 3.0mm		A4=3u"	B4=3u"			E: Tray
		A5=5u"	B5=5u"			
		A6=10u"	B6=10u"			
		A7=15u"	B7=15u"			
		A8=20u"	B8=20u"			
		A9=30u"	B9=30u"			
		S1=Ordinary Tin Plated				
		S2=Matte Tin Plated				
		S3=Tin-plated High-temperature				

RoHS
COMPLIANT

客编:

注意事项

- 带*为品质重点检验尺寸
- 打内K, 炉后0.3kgf Min

				OPERATION		SCALE		Fit	Yxcon 东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.			
				X.X	±0.25	UNIT		MM				
A1	2022.10.22	△	增加打内K	X.XX	±0.20	SIZE	A4	DESIGN	李官森2022.10.22	PART NO.	P125-1203A0CS155B1	
A0	2022.04.11	/	新版发行	X.XXX	±0.10	SHEET	1/1	CHECK		TITLE:	2.54排针 2*3P L=15.5/3.0 180度 打内K 炉后0.3kg PA9T料 镀金0.8u" CAP+230PCS/透明卷	
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	Angle	±3°	PROJ.	APPROVE			Customer No.		
				DIM	TOL							