





SECTION A-A



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围:  $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$ .
3. 额定电压: 30V, AC/DC.
4. 耐电压: 200V, AC/minute.
5. 接触电阻:  $\leq 0.02\Omega$ .
6. 绝缘电阻:  $\geq 100\text{M}\Omega$ .
7. 额定电流: 0.5A AC/DC.



| REV. | ECN NO.       | DESCRIPTION | DATE             | DESIGN |
|------|---------------|-------------|------------------|--------|
|      |               |             |                  |        |
|      |               |             |                  |        |
| 序号   | 品名            |             | 材质               |        |
| 1    | 0.8—C型卧式WTB胶芯 |             | LCP UL94 V—0 自然色 |        |
| 2    | 0.8—C型立式WTB端子 |             | 铜合金／表面镀锡         |        |
| 3    | 0.8—C型卧式WTB焊片 |             | 铜合金／表面镀锡         |        |

| Part No         | CKT | A     | B     |
|-----------------|-----|-------|-------|
| D-0.8-W1-M2P41  | 2   | 0.80  | 3.80  |
| D-0.8-W1-M3P41  | 3   | 1.60  | 4.60  |
| D-0.8-W1-M4P41  | 4   | 2.40  | 5.40  |
| D-0.8-W1-M5P41  | 5   | 3.20  | 6.20  |
| D-0.8-W1-M6P41  | 6   | 4.00  | 7.00  |
| D-0.8-W1-M7P41  | 7   | 4.80  | 7.80  |
| D-0.8-W1-M8P41  | 8   | 5.60  | 8.60  |
| D-0.8-W1-M9P41  | 9   | 6.40  | 9.40  |
| D-0.8-W1-M10P41 | 10  | 7.20  | 10.20 |
| D-0.8-W1-M11P41 | 11  | 8.00  | 11.00 |
| D-0.8-W1-M12P41 | 12  | 8.80  | 11.80 |
| D-0.8-W1-M13P41 | 13  | 9.60  | 12.60 |
| D-0.8-W1-M14P41 | 14  | 10.40 | 13.40 |
| D-0.8-W1-M15P41 | 15  | 11.20 | 14.20 |

| Part No         | CKT | A     | B     |
|-----------------|-----|-------|-------|
| D-0.8-W1-M16P41 | 16  | 12.00 | 15.00 |
| D-0.8-W1-M17P41 | 17  | 12.80 | 15.80 |
| D-0.8-W1-M18P41 | 18  | 13.60 | 16.60 |
| D-0.8-W1-M19P41 | 19  | 14.40 | 17.40 |
| D-0.8-W1-M20P41 | 20  | 15.20 | 18.20 |
| D-0.8-W1-M21P41 | 21  | 16.00 | 19.00 |
| D-0.8-W1-M22P41 | 22  | 16.80 | 19.80 |
| D-0.8-W1-M23P41 | 23  | 17.60 | 20.60 |
| D-0.8-W1-M24P41 | 24  | 18.40 | 21.40 |
| D-0.8-W1-M25P41 | 25  | 19.20 | 22.20 |
| D-0.8-W1-M26P41 | 26  | 20.00 | 23.00 |
| D-0.8-W1-M27P41 | 27  | 20.80 | 23.80 |
| D-0.8-W1-M28P41 | 28  | 21.60 | 24.60 |

| TOLERANCE |     | 深圳聚兴泰电子科技有限公司<br>Shenzhen Juxingtai Electronic Technology Co., Ltd |                    |       |
|-----------|-----|--------------------------------------------------------------------|--------------------|-------|
| X.±0.50   | ±1° | PART NO.                                                           | TITLE:             |       |
| X.X±0.20  |     | D-0.8-W1-MNP41                                                     | 0.80 Pitch C型卧式WTB |       |
| X.XX±0.10 |     | DESIGN: Ethan                                                      | MANUFACTURE DWG    |       |
| UNITS     | mm  | CHED: Olvia                                                        |                    | SCALE |
| MATERILA  | --- | APPD: Ava                                                          |                    | SHEET |
| FINISH    | --- |                                                                    | N:A                | 1/1   |