



序号	品名	材质
1	0.6-卧式WTB胶芯	LCP UL94 V-0 黑色
2	0.6-卧式WTB端子	铜合金/表面镀锡
3	0.6-卧式WTB焊片	铜合金/表面镀锡



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 105^{\circ}\text{C}$.
3. 额定电压: 30V, AC/DC.
4. 耐电压: 200V, AC/minute.
5. 接触电阻: $\leq 0.02\Omega$.
6. 绝缘电阻: $\geq 100\text{M}\Omega$.
7. 额定电流: 0.5A AC/DC.

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	CKT	A	B	C
D-0.6-W1-B2P41	2	0.60	1.40	3.10
D-0.6-W1-B3P41	3	1.20	2.00	3.70
D-0.6-W1-B4P41	4	1.80	2.60	4.30
D-0.6-W1-B5P41	5	2.40	3.20	4.90
D-0.6-W1-B6P41	6	3.00	3.80	5.50
D-0.6-W1-B7P41	7	3.60	4.40	6.10
D-0.6-W1-B8P41	8	4.20	5.00	6.70
D-0.6-W1-B9P41	9	4.80	5.60	7.30
D-0.6-W1-B10P41	10	5.40	6.20	7.90
D-0.6-W1-B11P41	11	6.00	6.80	8.50
D-0.6-W1-B12P41	12	6.60	7.40	9.10
D-0.6-W1-B13P41	13	7.20	8.00	9.70
D-0.6-W1-B14P41	14	7.80	8.60	10.30
D-0.6-W1-B15P41	15	8.40	9.20	10.90
D-0.6-W1-B16P41	16	9.00	9.80	11.50
D-0.6-W1-B17P41	17	9.60	10.40	12.10
D-0.6-W1-B18P41	18	10.20	11.00	12.70
D-0.6-W1-B19P41	19	10.80	11.60	13.30
D-0.6-W1-B20P41	20	11.40	12.20	13.90
D-0.6-W1-B21P41	21	12.00	12.80	14.50
D-0.6-W1-B22P41	22	12.60	13.40	15.10

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.±0.50	±1°	PART NO.	TITLE:	
X.X±0.20		D-0.6-W1-BNP41	0.60 Pitch 卧式WTB	
X.XX±0.10		DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		
MATERILA	---	APPD: Ava		
FINISH	---		SCALE	SHEET
			N:A	1/1