







技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$.
3. 额定电压: 30V, AC/DC.
4. 耐电压: 200V, AC/minute.
5. 接触电阻: $\leq 0.02\Omega$.
6. 绝缘电阻: $\geq 100M\Omega$.
7. 额定电流: 0.5A AC/DC.

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
序号	品名		材质	
1	0.8—C型卧式WTB胶芯		LCP UL94 V—0 自然色	
2	0.8—C型立式WTB端子		铜合金／表面镀锡	
3	0.8—C型卧式WTB焊片		铜合金／表面镀锡	
4	0.8—C型立式WTB吸盖		LCP UL94 V—0 黑色	



Part No	CKT	A	B
D-0.8-L1-M2P41	2	0.80	3.80
D-0.8-L1-M3P41	3	1.60	4.60
D-0.8-L1-M4P41	4	2.40	5.40
D-0.8-L1-M5P41	5	3.20	6.20
D-0.8-L1-M6P41	6	4.00	7.00
D-0.8-L1-M7P41	7	4.80	7.80
D-0.8-L1-M8P41	8	5.60	8.60
D-0.8-L1-M9P41	9	6.40	9.40
D-0.8-L1-M10P41	10	7.20	10.20
D-0.8-L1-M11P41	11	8.00	11.00
D-0.8-L1-M12P41	12	8.80	11.80
D-0.8-L1-M13P41	13	9.60	12.60
D-0.8-L1-M14P41	14	10.40	13.40
D-0.8-L1-M15P41	15	11.20	14.20

Part No	CKT	A	B
D-0.8-L1-M16P41	16	12.00	15.00
D-0.8-L1-M17P41	17	12.80	15.80
D-0.8-L1-M18P41	18	13.60	16.60
D-0.8-L1-M19P41	19	14.40	17.40
D-0.8-L1-M20P41	20	15.20	18.20
D-0.8-L1-M21P41	21	16.00	19.00
D-0.8-L1-M22P41	22	16.80	19.80
D-0.8-L1-M23P41	23	17.60	20.60
D-0.8-L1-M24P41	24	18.40	21.40
D-0.8-L1-M25P41	25	19.20	22.20
D-0.8-L1-M26P41	26	20.00	23.00
D-0.8-L1-M27P41	27	20.80	23.80
D-0.8-L1-M28P41	28	21.60	24.60

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	±1°	PART NO.	TITLE:		
X.X±0.20		D-0.8-L1-MNP41	0.80 Pitch C型立式WTB		
X.XX±0.10		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia			
MATERILA	---	APPD: Ava			
FINISH	---				
			SCALE	SHEET	
			N:A	1/1	