





REV.	ECN NO.	DESCRIPTION	DATE	DESIGN




技术指标:

1. 塑件表面应光洁, 无毛边, 无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$.
3. 额定电压: 150V AC/DC.
4. 额定电流: 1.0A AC/DC(AWG#28).
5. 接触电阻: $\leq 20\text{m}\Omega$ (Initial) per contact, $\leq 40\text{m}\Omega$ Change allowed.
6. 绝缘电阻: $\geq 500\text{M}\Omega$.
7. 耐压: 500V AC (Minute)

型号	CKT	A	B
D-DF1.25-L2-Y5P42	2*5	12.50	5.00
D-DF1.25-L2-Y6P42	2*6	13.75	6.25
D-DF1.25-L2-Y7P42	2*7	15.00	7.50
D-DF1.25-L2-Y8P42	2*8	16.25	8.75
D-DF1.25-L2-Y9P42	2*9	17.50	10.00
D-DF1.25-L2-Y10P42	2*10	18.75	11.25
.....			
D-DF1.25-L2-Y25P42	2*25	(25*1.25)+6.25	(25*1.25)-1.25



PCB.WELDING DRAWING (TOLERANCE:±0.05)



4	1.25A型双排立式吸盖	LCP UL94V-0 本色
3	1.25A型双排立式胶芯	PA6T UL94V-0 本色
2	1.25A型双排立式焊片	黄铜/表面镀锡80u" Min, 镀镍30u"Min
1	1.25A型双排立式端子	黄铜/表面镀锡80u" Min, 镀镍30u"Min
序号	名称	数量

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.30	X.*±5°	PART NO.	TITLE:		
.XX±0.25	X.X°±1°	D-DF1.25-L2-YNP42	1.25 Pitch A型(DF13)双排立式		
.XXX±0.15		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	— — —	APPD: Ava		N:A	1/1
FINISH	— — —				