





产品名称:绝缘粒



型号	A	B	C	D	E	备注
NDST-3	ø8.0±0.1	ø8.0±0.05	ø3.0±0.05	2.5±0.05	2.0±0.1	PBT
NDST-3-1	ø12±0.2	ø6.8±0.1	4.1±0.1	2.95±0.06	2.0±0.1	PBT
NDST-4	ø10±0.1	ø5±0.05	ø4.0±0.05	3.0±0.1	1.0±0.1	
NDST-220-5	ø6.1±0.1	ø3.55±0.05	02.9±0.05	1.0±0.1	1.0±0.1	NY66, ø2.9或ø3.0
NDST-220	ø6.1±0.1	ø3.55±0.02	3.0±0.02	1.5±0.05	1.1±0.1	PPS, NYW, NYA, PBT
NDST-8A						
NDST-8A-2	ø6.0±0.1	ø3.5±0.02	ø2.95±0.02	1.4±0.1	1.5±0.1	NY, PBT
NDST-220A	ø6.1±0.2	ø3.5±0.02	ø3.0±0.05	2.0±0.05	1.2±0.1	
NDST-220B	ø6.2±0.2	ø3.6±0.05	ø3.0±0.05	2.5±0.05	2.0±0.1	PPS, PBT, NTW, NYA
NDST-220C	ø6.1±0.1	ø3.5±0.02	ø3.0±0.05	2.0±0.05	2.0±0.05	PBT
NDST-220D	ø6.2±0.1	ø3.55±0.02	ø3.0±0.05	3.0±0.1	1.9±0.1	PPS
GSY0-220-D2.95	ø6.3±0.1	ø3.55±0.02	ø2.95±0.05	1.6±0.1	1.9±0.1	
NDST-220E (AK)	ø6.1±0.1	ø3.55±0.02	ø3.0±0.05	1.6±0.1	1.5±0.1	
NDST-220-H	ø6.1±0.1	ø3.5±0.02	ø3.0±0.05	3.5±0.1	1.1±0.1	PP
NDST-220HF	ø6.1±0.1	ø3.4±0.02	ø3.0±0.05	2.4±0.1	1.7±0.1	
NDST-220F	ø6.5±0.1	ø3.5±0.02	ø3.0±0.05	1.5±0.05	2.4±0.1	PBT
NDST-220R	ø6.1±0.1	ø3.55±0.02	ø3.0±0.05	1.5±0.05	1.1±0.1	
NDST-220S	ø6.0±0.1	ø3.5±0.02	ø2.95±0.02	1.5±0.05	1.1±0.1	NY66+25%, BPT
NDST-220-126	ø6.1±0.1	ø3.0±0.05	ø2.55±0.05	3.1±0.1	1.1±0.1	
NDST-220-NY46	ø6.1±0.1	ø3.55±0.02	ø3.0±0.02	1.5±0.05	1.2±0.1	
NDST-220HZ	ø6.2±0.1	ø3.55±0.05	ø3.0±0.05	3.0±0.1	1.8±0.1	
NDST-220K	ø6.1±0.1	ø3.6±0.05	ø2.95±0.02	3.5±0.1	1.1±0.1	
GST0-T型	ø12.2±0.2	ø6.6±0.1	ø4.15±0.1	4.9±0.1	2.0±0.1	
NDST-220PA	ø6.0±0.1	ø3.45±0.05	ø3.0±0.05	1.5±0.05	1.0±0.1	
NDST-220PD	ø6.0±0.1	ø3.5±0.02	ø3.0±0.05	1.5±0.05	1.1±0.1	
NDST-220M	ø5.7±0.1	ø3.55±0.05	ø3.0±0.05	1.7±0.1	1.0±0.1	MAN

材质：NY66 、 NY46 、 PPS 、 PBT 、 LCP 。
颜色：根据客户需要和原料而定
备注：