





2Pin



4Pin

GT-A5701 H M -2 XX X 01

G-Switch

Series No



Connector
H-Housing

M-Male


Housing Colour
B-Black

Pin Q' PY
02~12

Row NO
2-Dual Dows





6Pin




8Pin

G-Switch Specification:

- 1.Current rated: 23A AC/DC
- 2.Voltage rating: 600V AC/DC
- 3.Withstanding voltage: 2200V AC
- 4.Contact resistance: 10mΩ max.
- 5.Insulation resistance: 1000MΩ min
- 6.Durability cycle: 30Cycles
- 7.Removal force: 1.0kgf/Pin min
- 8.Operating temperature range: -40°C ~ +105°C



10Pin



12Pin

Ordering Information:

Circuit	Dimensions(mm)		Circuit	Dimensions(mm)	
	A	B		A	B
02	--	8.50	08	17.10	23.80
04	--	12.30	10	22.80	29.50
06	11.40	18.00	12	28.50	35.30

SCALE: 1:1 UNIT: mm
SIZE: A4

Title: Housing 5.70mm Pitch MX Dual Dows Male

Unless otherwise
General Tolerance:

X ±0.40
X.x ±0.30
X.xx ±0.20
X° ±5°
X.x° ±3°

Molde Code: GT-A5701HM-2XXX01

DRAWN	CHECKED	APPROVED	DATE
Hu	Chen	Chen	2021.10.20

品赞科技
b-Switch
www.dg-switch.com

REV: A0 SHEET: 1/1

1	HOUSING	PA66,94V-0	BLACK
NO.	PART NAME	MATERIAL	REMARK

