





REV.	ECN NO.	DESCRIPTION	DATE	DESIGN























Part No	CKT	A	B	C
BTB0867G-2*10PBL1	2*10	7.20	13.80	12.20
BTB0867G-2*11PBL1	2*11	8.00	14.60	13.00
BTB0867G-2*12PBL1	2*12	8.80	15.40	13.80
BTB0867G-2*13PBL1	2*13	9.60	16.20	14.60
BTB0867G-2*14PBL1	2*14	10.40	17.00	15.40
BTB0867G-2*15PBL1	2*15	11.20	17.80	16.20
BTB0867G-2*16PBL1	2*16	12.00	18.60	17.00
BTB0867G-2*17PBL1	2*17	12.80	19.40	17.80
BTB0867G-2*18PBL1	2*18	13.60	20.20	18.60
BTB0867G-2*19PBL1	2*19	14.40	21.00	19.40
BTB0867G-2*20PBL1	2*20	15.20	21.80	20.20
BTB0867G-2*21PBL1	2*21	16.00	22.60	21.00
BTB0867G-2*22PBL1	2*22	16.80	23.40	21.80
BTB0867G-2*23PBL1	2*23	17.60	24.20	22.60
BTB0867G-2*24PBL1	2*24	18.40	25.00	23.40
BTB0867G-2*25PBL1	2*25	19.20	25.80	24.20
...	...	...	...	...
BTB0867G-2*100PBL1	2*100	79.20	85.80	84.20


技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 100V, AC。
4. 接触电阻: $\leq 0.05\Omega$ 。
5. 绝缘电阻: $\geq 500M\Omega$ 。

序号	品名	材质	TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
①	0.8 Pitch B型立式 BTB公座胶芯	LCP UL94 V-0, 颜色:本色	X. ± 0.50	$\pm 1^{\circ}$	PART NO. BTB0867G-2*NPBL1	TITLE: 0.8 Pitch B型立式 BTB公座业务图(单高6.7)			
②	0.8 Pitch B型立式 BTB公座端子	铜合金/表面点镀金	X.X ± 0.20						
③	0.8 Pitch B型立式 BTB公座吸盖	不锈钢	X.XX ± 0.10						
			UNITS	mm	DESIGN:	Ethan	MANUFACTURE DWG		
			MATERILA	— — —	CHED:	Olvia		SCALE	SHEET
			FINISH	— — —	APPD:	Ava		N:A	1/2

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

公座 (PLUG) 母座 (SOCKET)				
				
				
				
				

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	±1°	PART NO.	TITLE: 0.8 Pitch B型立式		
X.X±0.20		BTB0867G-2*NPBL1	BTB公座业务图(单高6.7)		
X.XX±0.10		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	— — —	APPD: Ava		N:A	2/2