








技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

合高(H)	公座单高	母座单高
3.0	2.2	2.2
3.5	2.2	2.7
4.0	2.2	3.2
5.0	2.6	4.4

Part No	CKT	A	B	C	D	E
BTB0522M-2*5PBL3	2X5	2.00	3.20	4.70	6.06	4.10
BTB0522M-2*6PBL3	2X6	2.50	3.70	5.20	6.56	4.60
BTB0522M-2*7PBL3	2X7	3.00	4.20	5.70	7.06	5.10
BTB0522M-2*8PBL3	2X8	3.50	4.70	6.20	7.56	5.60
BTB0522M-2*9PBL3	2X9	4.00	5.20	6.70	8.06	6.10
BTB0522M-2*10PBL3	2X10	4.50	5.70	7.20	8.56	6.60
BTB0522M-2*11PBL3	2X11	5.00	6.20	7.70	9.06	7.10
BTB0522M-2*12PBL3	2X12	5.50	6.70	8.20	9.56	7.60
BTB0522M-2*13PBL3	2X13	6.00	7.20	8.70	10.06	8.10
BTB0522M-2*14PBL3	2X14	6.50	7.70	9.20	10.56	8.60
BTB0522M-2*15PBL3	2X15	7.00	8.20	9.70	11.06	9.10
BTB0522M-2*16PBL3	2X16	7.50	8.70	10.20	11.56	9.60
BTB0522M-2*17PBL3	2X17	8.00	9.20	10.70	12.06	10.10
BTB0522M-2*18PBL3	2X18	8.50	9.70	11.20	12.56	10.60
BTB0522M-2*19PBL3	2X19	9.00	10.20	11.70	13.06	11.10
BTB0522M-2*20PBL3	2X20	9.50	10.70	12.20	13.56	11.60
BTB0522M-2*22PBL3	2X22	10.50	11.70	13.20	14.56	12.60
BTB0522M-2*25PBL3	2X25	12.00	13.20	14.70	16.06	14.10
BTB0522M-2*30PBL3	2X30	14.50	15.70	17.20	18.56	16.60
BTB0522M-2*35PBL3	2X35	17.00	18.20	19.70	21.06	19.10
BTB0522M-2*40PBL3	2X40	19.50	20.70	22.20	23.56	21.60

序号	品名	材质	TOLERANCE			深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
①	0.5 Pitch B型 单槽立式BTB母座胶芯	LCP UL94 V-0 颜色:米黄色	X.±0.50	±1°		PART NO.	TITLE: 0.5 Pitch B型单槽 立式BTB母座业务图(单高2.2)		
②	0.5 Pitch B型 单槽立式BTB母座端子	铜合金/表面镀锡/表面点镀金	X.X±0.20		BTB0522M-2*NPBL3	MANUFACTURE DWG			
			X.XX±0.10						
③	0.5 Pitch B型 单槽立式BTB母座焊片	铜合金/表面镀锡	UNITS	mm	DESIGN: Ethan				
			MATERILA	— — —	CHED: Olvia				
			FINISH	— — —	APPD: Ava		SCALE	SHEET	
						N:A	1/1		